

**Modlink MSDD-set: Frame 4000-68523-0000001,**

insert 4000-68000-4120000

Art.No.: 4000-68523-4120001

Weight: 0.541


Country of origin: US

Model designation: MSDD\_2metallic\_GFCI 15A+2xRJ45+3A fuse\_

with touch protection

[Link to Product](#)**Illustration**

Product may differ from Image



0  
0  
0  
0  
0  
0  
0



0  
0  
0  
0  
0  
0  
0  
0  
0  
0

Commercial data	
URL Webshop	<a href="https://shop.murrelektronik.com/4000-68523-4120001">https://shop.murrelektronik.com/4000-68523-4120001</a>
GTIN	4048879477970
ECLASS-6.0	27144001
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
EAN	4048879477970
Mechanical data   Mounting data	
Height	88 mm
Width	116 mm
Depth	72 mm
Frame	
Material housing	PA
Color housing	black
Material lid	ABS
Color cover	metallic
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65

Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Storage temperature min.	-30 °C

#### Fuse

Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A

#### USA

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	yes
Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A

#### RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA