

MSDD pass-through USB 3.0 form A, 0.6 m cable, design silver

Art.No.: 4000-73000-0150000

Weight: 0.059 kg

Country of origin: CZ




Model designation: MSDD PT22-S USB3.0 A/A F/M_0.6


Pass-through

1 × USB 3.0 (female/male/0.6 m cable) form A


[Link to Product](#)

Illustration





Product may differ from Image

**Commercial data**

URL Webshop	https://shop.murrelektronik.com/4000-73000-0150000
GTIN	4048879432894
ECLASS-6.0	27143423
ECLASS-6.1	27143419
ECLASS-7.0	27440515
ECLASS-7.1	27440515
ECLASS-8.0	27440515
ECLASS-8.1	27440515
ECLASS-9.0	27440515
ECLASS-9.1	27440515
ECLASS-10.0.1	27440515
ECLASS-10.1	27440515
ECLASS-11.0	27440515
ECLASS-11.1	27440515
ECLASS-12.0	27440515
ECLASS-13.0	27440515
ECLASS-14.0	27440515
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85444290
EAN	4048879432894
Packaging unit	1

Electrical data | Supply

Operating voltage AC	5 V
Operating voltage DC	5 V
Operating current max.	900 mA

Industrial Communication

Data transmission rate max.	5.000 Mbit/s
USB specification	3.0

Device protection

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-05-05

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Shielded Yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20, IP65
Protection NEMA	12, 3R, 4x, 4, 13, 2
Additional condition protection degree	in closed state, inserted

Device protection | Mechanical

Mechanical endurance	1.500 cycles
----------------------	--------------

Mechanical data | Mounting data

Depth	30 mm
Diameter	29,5 mm
Mounting depth	70 mm
Diameter cutout	22,5 mm

Approvals

UL 50E	Yes
--------	-----