

blue,green,amber,red,buzzer

Weight: 0.475

Country of origin: ID

Model designation: Modlight70 Pro BASE LED-BGYR BUZZER

Basis, buzzer, LED modules

red, yellow, green, blue

Illustration



CE



Material short text	Modlight70 Pro BASE LED-BGYR BUZZER
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-76702-6531000
GTIN	4048879759915
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-7.1	27371230
ECLASS-8.0	27371230
ECLASS-8.1	27371230
ECLASS-9.0	27371230
ECLASS-9.1	27371230
ECLASS-10.0.1	27371230
ECLASS-10.1	27371230
ECLASS-11.0	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ECLASS-13.0	27371230
ECLASS-14.0	27371230

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ETIM-5.0	EC001042
ETIM-6.0	EC001042
ETIM-7.0	EC001042
ETIM-8.0	EC001042
customs tariff number	85318070
EAN	4048879759915
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21.6 V
Operating voltage DC max.	26.4 V
Current consumption max.	430 mA

HMI

Buzzer sound	fast beep, continuous beep, fast high-low, sweep tone
Sound pressure at 1 m	90 dB
Reduced sound pressure at 1 m	80 dB

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

Material housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	334 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C