

Signal tower Modlight70 Pro equipped with LED modules

green,amber,red,buzzer,M12 plug downward

Art.No.: 4000-76705-5310000

Weight: 0.470 kg

Country of origin: CZ

Model designation: Modlight70 Pro BASE M12-8U LED-GYR BUZ.


Basic, buzzer, flash + LED modules + M12 (down)
green, yellow, red

Link to Product

Illustration



Product may differ from Image



Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-76705-5310000
GTIN	4048879759939
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-7.1	27371230
ECLASS-8.0	27371230
ECLASS-8.1	27371230
ECLASS-9.0	27371230
ECLASS-9.1	27371230
ECLASS-10.0.1	27371230
ECLASS-10.1	27371230
ECLASS-11.0	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ECLASS-13.0	27371230
ECLASS-14.0	27371230
ETIM-5.0	EC001042
ETIM-6.0	EC001042

ETIM-7.0	EC001042
ETIM-8.0	EC001042
customs tariff number	85318070
EAN	4048879759939
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	385 mA

HMI

Buzzer sound	fast beep, continuous beep, fast high-low, sweep tone
Sound pressure at 1 m	90 dB
Reduced sound pressure at 1 m	80 dB

HMI | Illumination properties

Blink cycles	60 ±12 per minute
--------------	-------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	293 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C