

ETIM-5.0	EC001042
ETIM-6.0	EC001042
ETIM-7.0	EC001042
ETIM-8.0	EC001042
customs tariff number	85318070
EAN	4048879759939
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21.6 V
Operating voltage DC max.	26.4 V
Current consumption max.	385 mA

HMI

Buzzer sound	fast beep, continuous beep, fast high-low, sweep tone
Sound pressure at 1 m	90 dB
Reduced sound pressure at 1 m	80 dB

HMI | Illumination properties

Blink cycles	60 ±12 per minute
--------------	-------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

Mechanical data | Material data

Material housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	293 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C