

M8 male 0° A-cod. IDC3-pol., 0,25 - 0,5mm², 2,5 - 5mm

Art.No.: 7000-08325-0000000

Weight: 0.008 kg




Country of origin: DE

Model designation: MSHL0-AC-R IDC 0,25-0,5mm²

IDC terminals

Male straight

M8, 3-pole

Connection cross section: 0.25...0.5 mm²[Link to Product](#)**Illustration**

Product may differ from image

**Header**

Material short text

MSHL0-AC-R IDC 0,25-0,5mm²**Side 1**

Family construction form	M8
No. of poles	3
Gender	male
Mounting method	inserted, screwed
Cable outlet	straight
Material	PA
Material contact	Copper alloy
Degree of protection (EN IEC 60529)	IP67, IP65

Side 2

Mounting method	Field-wireable
-----------------	----------------

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-08325-0000000
-------------	---

GTIN	4048879784689
------	---------------

ECLASS-6.0	27279221
------------	----------

ECLASS-6.1	27260702
------------	----------

ECLASS-7.0	27440102
------------	----------

ECLASS-7.1	27440102
------------	----------

ECLASS-8.0	27440102
------------	----------

ECLASS-8.1	27440102
------------	----------

ECLASS-9.0	27440116
------------	----------

ECLASS-9.1	27440106
------------	----------

ECLASS-10.0.1	27440106
---------------	----------

ECLASS-10.1	27440102
-------------	----------

ECLASS-11.0	27440106
-------------	----------

ECLASS-11.1	27440102
-------------	----------

ECLASS-12.0	27440116
-------------	----------

ECLASS-13.0	27440106
-------------	----------

ECLASS-14.0	27440106
-------------	----------

ETIM-5.0	EC002635
----------	----------

ETIM-6.0	EC002635
----------	----------

ETIM-7.0	EC002635
----------	----------

ETIM-8.0	EC002635
----------	----------

customs tariff number	85366990
-----------------------	----------

EAN	4048879784689
-----	---------------

Packaging unit	1
----------------	---

customs tariff number	85366990
-----------------------	----------

EAN	4048879784689
-----	---------------

Packaging unit	1
----------------	---

Electrical data | Supply

Operating voltage AC max.	48 V
---------------------------	------

Operating voltage DC max.	60 V
---------------------------	------

Current operating per contact max.	4 A
------------------------------------	-----

Installation

Connection cross section min.	0,25 mm ²
-------------------------------	----------------------

Connection cross section max.	0,5 mm ²
-------------------------------	---------------------

Installation | Connection

Connection	Cut clamps IDC
------------	----------------

Tightening torque	0,4 Nm
-------------------	--------

Mounting set	M8 x 1
--------------	--------

Mating cycles min.	100
--------------------	-----

Wire insulation diameter min.	1,1 mm
-------------------------------	--------

Wire insulation diameter max. 1,55 mm

Device protection | Electrical

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Overtoltage category (EN 60950-1)	II
Rated surge voltage	0,8 kV
Insulation resistance min.	100 mΩ
Material group (IEC 60664-1)	III

Mechanical data | Material data

Material contact carrier	TPU
Coating contact	gold plated
Locking material	Zinc die-casting
Coating locking	Nickelated
Material gasket	NBR

Mechanical data | Mounting data

Mounting method	Hexagonal screw, Hexagonal nut
Looking techniques	Schraubgewinde
Clamping range min.	2,5 mm
Clamping range max.	5 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	80 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard	EN IEC 61076-2-114 (M8)
------------------	-------------------------