

M8 female 0° A-cod. IDC

 3-pol., 0,25 - 0,5mm², 2,5 - 5mm

Art.No.: 7000-08365-0000000

Weight: 0.007 kg




Country of origin: DE

 Model designation: MSFL0-AC-R IDC 0,25-0,5mm²

IDC terminals

Female straight

M8, 3-pole

 Connection cross section: 0.25...0.5 mm²
[Link to Product](#)
Illustration


Product may differ from image


Header

Material short text

 MSFL0-AC-R IDC 0,25-0,5mm²
Side 1

Family construction form	M8
No. of poles	3
Gender	female
Mounting method	inserted, screwed
Cable outlet	straight
Material	PA
Material contact	Copper alloy
Degree of protection (EN IEC 60529)	IP67, IP65
Side 2	
Mounting method	Field-wireable
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-08365-0000000
GTIN	4048879784801
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879784801
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	48 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Installation	
Connection cross section min.	0,25 mm ²
Connection cross section max.	0,5 mm ²
Installation Connection	
Connection	Cut clamps IDC
Mounting set	M8 x 1
Mating cycles min.	100
Wire insulation diameter min.	1,1 mm
Wire insulation diameter max.	1,55 mm
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Pollution Degree	3

Overvoltage category (EN 60950-1)	II
Rated surge voltage	0,8 kV
Insulation resistance min.	100 mΩ
Material group (IEC 60664-1)	III

Mechanical data | Material data

Material contact carrier	TPU
Coating contact	gold plated
Locking material	Zinc die-casting
Coating locking	Nickelated
Material gasket	NBR

Mechanical data | Mounting data

Mounting method	Hexagonal screw, Hexagonal nut
Looking techniques	Schraubgewinde
Clamping range min.	2,5 mm
Clamping range max.	5 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	80 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard	EN IEC 61076-2-114 (M8)
------------------	-------------------------