

**M8 male 0° A-cod. IDC**3-pol., 0,25 - 0,5mm<sup>2</sup>, 2,5 - 5mm

Art.No.: 7000-08325-0000000

Weight: 0.008



Country of origin: DE

Model designation: MSHL0-AC-R IDC 0,25-0,5mm<sup>2</sup>


IDC terminals

Male straight

M8, 3-pole

Connection cross section: 0.25...0.5 mm<sup>2</sup>[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MSHL0-AC-R IDC 0,25-0,5mm<sup>2</sup>**Side 1**

Family construction form	M8
No. of poles	3
Mounting method	inserted, screwed
Material	PA
Material contact	Copper alloy
Degree of protection (EN IEC 60529)	IP67, IP65

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/7000-08325-0000000">https://shop.murrelektronik.com/7000-08325-0000000</a>
GTIN	4048879784689
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879784689
Packaging unit	1

#### Electrical data | Supply

Operating voltage AC max.	48 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A

#### Installation

Connection cross section min.	0.25 mm <sup>2</sup>
Connection cross section max.	0.5 mm <sup>2</sup>

#### Installation | Connection

Connection	Cut clamps IDC
Mounting set	M8 x 1
Mating cycles min.	100
Wire insulation diameter min.	1.1 mm
Wire insulation diameter max.	1.55 mm

#### Device protection | Electrical

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Overvoltage category (EN 60950-1)	II
Rated surge voltage	0.8 kV
Insulation resistance min.	100 mΩ
Material group (IEC 60664-1)	III

#### Mechanical data | Material data

Material contact carrier	TPU
Coating contact	gold plated
Locking material	Zinc die-casting
Coating locking	Nickeled
Material gasket	NBR

#### Mechanical data | Mounting data

Mounting method	Hexagonal screw, Hexagonal nut
Locking techniques	Schraubgewinde
Clamping range min.	2.5 mm
Clamping range max.	5 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	80 °C

#### Important installation notes

Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

#### Conformity

Product standard	DIN EN 61076-2-114 (M8)
------------------	-------------------------