

M8 male recept. A-cod. front incl. nut

PUR-wires 3x0.25 0.5m

Art.No.: 7000-08553-9700050

Weight: 0.022 Country of origin: DE


Model designation: MSHFV-R970_0.5


Flange M8 male with multi-strand wire 3-pole


Link to Product

Illustration














Product may differ from Image



Header	
Material short text	MSHFV-R970_0.5
Cable length	0,50 m
Side 1	
Family construction form	M8
No. of poles	3
Coding	A
Mounting method	inserted, screwed
Thread	M8 x 1
Tightening torque	0.4 Nm
Width across flats	SW10
Material	Brass
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-08553-9700050
GTIN	4048879508100
ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440103
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440103
ECLASS-11.0	27440109
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440109
ECLASS-14.0	27440109
ETIM-5.0	EC001855
ETIM-6.0	EC001855

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-04



EC001855 85444290
4040070500400
4048879508100
1
50 V
60 V
4 A
no
M8 x 1
IP67
6P. 4, 3
inserted, screwed
3
1.5 kV
Brass
nickel plated
Brass
nickel plated
Schraubgewinde
Schraubgewinde
-30 °C
85 °C
depending on cable quality
Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
yes
970
PP
3
1.1 mm
0.25 mm ²
-40 °C
90 °C
-25 °C