

**M8 male recept. A-cod. front incl. nut**

PUR-wires 3x0.25 0.5m




Art.No.: 7000-08553-9700050


Weight: 0.022 kg

Country of origin: DE


Model designation: MSHFV-R970\_0.5

Flange M8 male  
with multi-strand wire  
3-pole

[Link to Product](#)Illustration



Product may differ from Image



#### Header

Material short text MSHFV-R970\_0.5

Cable length 0,50 m

#### Side 1

Family construction form M8

No. of poles 3

Coding A

Mounting method inserted, screwed

Threaded hole M8 x 1

Tightening torque 0,4 Nm

Width across flats SW10

Material Brass

Degree of protection (EN IEC 60529) IP67

#### Commercial data

URL Webshop <https://shop.murrelektronik.com/7000-08553-9700050>

GTIN 4048879508100

ECLASS-6.0 27279220

ECLASS-6.1 27279220

ECLASS-7.0 27440103

ECLASS-7.1 27440103

ECLASS-8.0 27440103

ECLASS-8.1 27440103

ECLASS-9.0 27440103

ECLASS-9.1 27440109

ECLASS-10.0.1 27440109

ECLASS-10.1 27440103

ECLASS-11.0 27440109

ECLASS-11.1 27440103

ECLASS-12.0 27440103

ECLASS-13.0 27440109

ECLASS-14.0 27440109

ETIM-5.0 EC001855

ETIM-6.0 EC001855

ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879508100
Packaging unit	1

#### Electrical data | Supply

Operating voltage AC max.	50 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A

#### Diagnostics

Status indication LED	No
-----------------------	----

#### Installation | Connection

Mounting set	M8 x 1
--------------	--------

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Protection NEMA	6P, 4, 3
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Material group (IEC 60664-1)	I

#### Mechanical data | Material data

Material screw connection	Brass
Coating of fitting	nickel plated
Locking material	Brass
Coating locking	nickel plated

#### Mechanical data | Mounting data

Mounting method	Schraubgewinde
Looking techniques	Schraubgewinde

#### Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

#### Important installation notes

Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

#### Approvals

UL 50E	Yes
--------	-----

#### Installation | Cable

Cable identification	970
Wire arrangement	brown, black, blue
Material wire insulation	PP
Amount wires	3
Outer diameter insulation	1,1 mm
Conductor crosssection (wire)	0,25 mm <sup>2</sup>
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	90 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	90 °C
Bending radius (fixed)	5 x Outer diameter