

M8 female 0° A-cod. screw terminal4-pol., 0,14 - 0.5mm², 2,5 - 5mm

Art.No.: 7000-08631-0000000

Weight: 0.02



Country of origin: CN

Model designation: M8 BUCHSE GER. 2,5..5 4pol.


Female straight

M8, 4-pole

Screw terminal

Connection cross section: 0.14...0.5 mm²[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

M8 BUCHSE GER. 2,5..5 4pol.

Side 1

Family construction form	M8
No. of poles	4
Width across flats	SW13
Material contact	Brass
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP67

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-08631-0000000
GTIN	4048879224505
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879224505
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	50 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A

Installation

Connection cross section min.	0.14 mm ²
Connection cross section max.	0.5 mm ²

Installation | Connection

Connection	Screw terminals SK
------------	--------------------

Installation | Pin assignment

Coding	A
--------	---

Device protection | Electrical

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Overvoltage category (EN 60664-1)	III
Overvoltage category (EN 60950-1)	II
Rated surge voltage	15 kV
Insulation resistance min.	100 mΩ

Mechanical data | Material data

Material housing	PBT
------------------	-----

Material contact carrier PA66

Mechanical data | Mounting data

Height	45 mm
Width	12 mm
Depth	12 mm
Clamping range min.	25 mm
Clamping range max.	5 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.