

## MSUD valve plug BI-11mm 180° with cable

PVC 3x0.75 ye 5m

Art.No.: 7000-11081-0160500

Weight: 0.307 kg Country of origin: CZ

Model designation: MSUDK-KB1Z-016 5.0

**MSUD** 

Form BI (11 mm)

24 V AC ±20% / DC ±25%

LED and suppression

PE opposite cable entry (180°)

Attention: Contact carrier turned to 180°!

Further cable lengths on request.


Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


## **Link to Product**

## Illustration













stay connected







Product may differ from Image









Header	
Material short text	MSUDK-KB1Z-016_5.0
Cable length	5,00 m
Side 1	
Family construction form	Valve connector form BI
No. of poles	3
Gender	female
Mounting method	inserted, screwed
Threaded hole	M3x31
Tightening torque	0,4 Nm
Material	PBT
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-11081-0160500
GTIN	4048879220460
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218



stay connected

27279218 27279218 27279218 27060312 27060312 27060312 27060312 27060312 27060312 27060312 27060312 27060312
27279218 27060312 27060312 27060312 27060312 27060312 27060312 27060312
27060312 27060312 27060312 27060312 27060312 27060312 27060312
27060312 27060312 27060312 27060312 27060312 27060312
27060312 27060312 27060312 27060312
27060312 27060312 27060312 27060312
27060312 27060312 27060312
27060312 27060312
27060312
27060312
EC001855
EC001855
EC001855
EC001855
85444290
4048879220460
1
20 ms
24 V
19,2 V
28,8 V
24 V
18 V
30 V
4 A
55 V
15 mA
yellow
yollow
M3x31
inserted, screwed
3
Diode, Z-Diode
0,8 kV
I
black
Steel
galvanized
Steel
galvanized
PUR
1 011
inserted, screwed



stay connected

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Installation   Cable	
Cable identification	016
Cable Type	1
Amount stranding	1
Stranding	3 wires stranded
Cable weigth	58 g/m
Material wire insulation	PVC
Amount wires	3
Outer diameter insulation	1,8 mm
Outer diameter tolerance core insulation	± 0,1 mm
Shore hardness wire insulation	43 ± 5 Shore D
Material properties wire insulation	good machinability
ngredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Printing color of wire insulation	white (isolation black)
Amount strands (wire)	24
Diameter of single wires	0,2 mm
Conductor crosssection (wire)	0,75 mm²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Outer-diameter (jacket)	5,9 mm
Tolerance outer diameter (sheath)	±5%
Material jacket	PVC
Shore hardness jacket	80 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Material property (jacket)	good machinability
Conductor resistance (wire)	26 Ω/km @ 20 °C
Max. rated voltage (conductor - ground)	300 V
Max. rated voltage (conductor - conductor)	500 V
Withstand voltage (wire - wire)	3 kV @ 60 s
Withstand voltage (wire - jacket)	3 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	12 A
Min. operating temperature (static)	-30 °C
Max. operating temperature (static)	70 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	70 °C
Dil resistance	good
Chemical resistance	good
Other resistances	good resistance to gasoline
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter