

M12 male 0° A-cod. with cable

PVC 4x0.34 bk UL/CSA 5m

Art.No.: 7000-12021-6140500

Weight: 0.200 kg

Country of origin: US

Model designation: MSAL0-T614_5.0

Male straight





M12, 4-pole


with cable sleeves

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)
Illustration




Product may differ from Image



Header

Material short text	MSAL0-T614_5.0
---------------------	----------------

Cable length	5,00 m
--------------	--------

Side 1

Family construction form	M12
--------------------------	-----

No. of poles	4
--------------	---

Coding	A
--------	---

Gender	male
--------	------

Mounting method	inserted, screwed
-----------------	-------------------

Threaded hole	M12 x 1
---------------	---------

Tightening torque	0,6 Nm
-------------------	--------

Width across flats	SW13
--------------------	------

Cable outlet	straight
--------------	----------

suitable for corrugated tube (internal Ø)	10 mm
---	-------

Material	PUR
----------	-----

Material contact	Copper alloy
------------------	--------------

Coating contact	gold plated
-----------------	-------------

Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
-------------------------------------	-------------------

Side 2

Family construction form	free cable end
--------------------------	----------------

Stripping length (jacket)	20 mm
---------------------------	-------

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-12021-6140500
-------------	---

GTIN	4048879218047
------	---------------

ECLASS-6.0	27279218
------------	----------

ECLASS-6.1	27279218
------------	----------

ECLASS-7.0	27279218
------------	----------

ECLASS-7.1	27279218
------------	----------

ECLASS-8.0	27279218
------------	----------

ECLASS-8.1	27279218
------------	----------

ECLASS-9.0	27060311
------------	----------

ECLASS-9.1	27060311
------------	----------

ECCLASS-10.0.1	27060311
ECCLASS-10.1	27060311
ECCLASS-11.0	27060311
ECCLASS-11.1	27060311
ECCLASS-12.0	27060311
ECCLASS-13.0	27060311
ECCLASS-14.0	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879218047
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	4 A

Diagnostics

Status indication LED	No
-----------------------	----

Installation | Connection

Mounting set	M12 x 1
--------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	2,5 kV
Material group (IEC 60664-1)	I

Mechanical data | Material data

Material screw connection	Zinc die-casting
Coating of fitting	nickel plated
Locking material	Zinc die-casting
Coating locking	Nickelized

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard	EN IEC 61076-2-101 (M12)
------------------	--------------------------

Installation | Cable

Cable identification	614
Cable Type	1
Stranding	1 x 4 wires stranded
Wire arrangement	brown, black, blue, white
Cable weight	37 g/m

Material wire insulation	PVC
Amount wires	4
Outer diameter insulation	1,25 mm
Outer diameter tolerance core insulation	± 0,05 mm
Shore hardness wire insulation	45 ± 5 Shore D
Material properties wire insulation	good machinability
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Amount strands (wire)	19
Diameter of single wires	0,15 mm
Conductor crosssection (wire)	0,34 mm ²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Outer-diameter (jacket)	5 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PVC
Shore hardness jacket	85 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Material property (jacket)	good machinability
Conductor resistance (wire)	57 Ω/km @ 20 °C
Nominal voltage max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity max. (wire)	4,8 A
Operating temperature min. (static)	-30 °C
Operating temperature max. (static)	80 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	80 °C
Flame resistance	UL 1581 § 1080, CSA FT1, IEC 60332-1-2
Oil resistance	good
Chemical resistance	good
Other resistances	good resistance to gasoline
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter