

stay connected

M12 male duo 0° A-cod. screw terminal

4-pol., max. 0,75mm², 2,1 - 3mm, 4 - 5mm

Art.No.: 7000-12781-0000000

Weight: 0.024 Country of origin: DE

Model designation: MSA-T11D

Male straight

Y-connector M12, 4-pole

Screw terminals

Sealing range (cable Ø): 2.1...3/4...5 mm

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


clamping range 2.1...3/4...5 mm (2 cable bushings)


Link to Product

Illustration









Product may differ from Image





Header



Material short text	MSA-T11D

Material Short text	WOATTE
Side 1	
Family construction form	M12
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-12781-0000000
GTIN GTIN	4048879201629
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879201629
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	4 A
Installation	
Connection cross section max.	0.75 mm²
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data Mounting data	
	63 mm
Height Width	20 mm
Depth	20 mm
·	
Environmental characteristics Climat	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.