

M12 male 90° A-cod. screw terminal4-pol., max. 0,75mm², 4 - 6mm

Art.No.: 7000-12821-0000000

Weight: 0.023

Country of origin: DE

Model designation: MSC-T7

Male 90°



M12, 4-pole

Screw terminals


Sealing range (cable Ø): 4...6 mm

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MSC-T7

Side 1

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
Mounting method	pluggable, inserted
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW18
Degree of protection (EN IEC 60529)	IP67

Side 2

Mounting method	field-wireable
-----------------	----------------

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-12821-0000000
GTIN	4048879201605
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879201605
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	4 A

Diagnostics

Status indication LED	no
-----------------------	----

Installation

Rotation option	90° (4 outlet directions)
Connection cross section max.	0.75 mm²

Installation | Connection

Tightening torque	0.6 Nm
-------------------	--------

Installation | Pin assignment

Configuration	partly used
---------------	-------------

Device protection | Electrical

Additional condition protection degree inserted, screwed

Mechanical data | Mounting data

Height	41 mm
Width	41 mm
Depth	20 mm
Mounting method	inserted, screwed, Shaking protection
Clamping range min.	4 mm
Clamping range max.	6 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.