

Bus terminating plug M12 male A-cod.



Devicenet

Art.No.: 7000-13461-0000000
Weight: 0.012
Country of origin: DE
Model designation: MSA05L0-5 4-5R


DeviceNet, CANopen
Terminating resistor
Male
M12 – M12, 5-pole (circuit diagram)
A-coded

Link to Product

Illustration



Product may differ from Image















Side 1	
Family construction form	M12
No. of poles	5

Width across flats	SW13
Degree of protection (EN IEC 60529)	IP67
Commercial data	
ECLASS-6.0	19070403
ECLASS-6.1	19070403
ECLASS-7.0	19070403
ECLASS-8.0	19070403
ECLASS-9.0	19070403
ECLASS-10.1	19070403
ECLASS-11.1	19070403
ECLASS-12.0	19070403
ETIM-5.0	EC001855
customs tariff number	85332100
customs tariff number	85332100
GTIN	4048879198769
GTIN	4048879198769
Packaging unit	1
Packaging unit	1
Electrical data Supply	
Operating voltage DC max.	30 V
Operating voltage DC max. (UL-listed)	30 V
Current operating per contact max.	4 A
Installation Connection	
Tightening torque	0,6 Nm
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I
Mechanical data Material data	
Material housing	PUR
Coating locking	Nickel
Locking material	Zinc die-casting
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C