

M12 male recept. A-cod. front incl. nut

PUR-wires 4x0.34 0.2m

Art.No.: 7000-13502-9710020

Weight: 0.017 kg

Country of origin: DE

Model designation: MSAFV-T971_0.2

Flange male




M12, 4-pole



Front mounting

with multi-strand wire

Further cable lengths on request.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)
Illustration




Toleranz Kabellängen:
cable length tolerances

0m < L ≤ 0,5m	+0,03m	1,0m < L ≤ 3,0m	+0,1m
0,5m < L ≤ 1,0m	+0,05m	3,0m < L	±1,5%

Product may differ from Image



Header

Cable length 0,20 m

Side 1

Family construction form M12

No. of poles 4

Coding A

Mounting method inserted, screwed

Threaded hole M12 x 1

Tightening torque 0,6 Nm

Material Zinc die-casting

Material contact Copper alloy

Coating contact gold plated

Degree of protection (EN IEC 60529) IP67

Commercial data

URL Webshop <https://shop.murrelektronik.com/7000-13502-9710020>

customs tariff number 85444290

EAN 4048879494144

Packaging unit 1

Electrical data | Supply

Operating voltage AC max. 250 V

Operating voltage DC max. 250 V

Current operating per contact max. 4 A

Diagnostics

Status indication LED No

Installation | Connection

Mounting set M16 x 1.5

Width across flats SW19

Device protection | Electrical

Protection NEMA 6P, 4, 3

Additional condition protection degree inserted, screwed

Pollution Degree 3

Rated surge voltage 2,5 kV

Material group (IEC 60664-1)

I

Mechanical data

Contour for corrugated hose

without

Mechanical data | Material data

Coating housing

nickel plated

Material screw connection

Zinc die-casting

Coating of fitting

nickel plated

Locking material

Zinc die-casting

Coating locking

Nickel plated

Mechanical data | Mounting data

Mounting method

Schraubgewinde

Looking techniques

Schraubgewinde

Environmental characteristics | Climatic

Operating temperature min.

-30 °C

Operating temperature max.

85 °C

Additional condition temperature range

depending on cable quality

Important installation notes

Note on bending radius

Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Note on strain relief

Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Conformity

Product standard

EN IEC 61076-2-101 (M12)

Approvals

UL 50E

Yes

Installation | Cable

Cable identification

971

Cable weight

33 g/m

Material wire insulation

PUR

Amount wires

4

Outer diameter insulation

1,3 mm

Conductor crosssection (wire)

0,34 mm²

Operating temperature min. (static)

-40 °C

Operating temperature max. (static)

90 °C

Operating temperature min. (dynamic)

-25 °C

Operating temperature max. (dynamic)

90 °C

Bending radius (fixed)

5 × Outer diameter