

M12 male 0° Y-cod. with cable shielded



PUR AWG20/26 shielded bk UL/CSA+drag ch. 3m


Art.No.: 7000-15501-8050300

Weight: 0.32


Country of origin: CZ

Model designation: MSYAL0-08D805_3.0-ZS

Link to Product**Illustration**



Product may differ from Image



1

Side 1	
Family construction form	M12
No. of poles	8
Coding	Y
Gender	male
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW13
Cable outlet	straight
Material	PUR
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP65, IP66K, IP67
Side 2	
Family construction form	free cable end
Stripping length (jacket)	80 mm
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-15501-8050300
EAN	4048879519311
Electrical data Supply	
Operating voltage AC max.	50 V
Operating voltage DC max.	50 V
Operating current per data contact max.	0.5 A
Operating current per power contact max.	6 A
Industrial communication	
Data transmission rate max.	100 MBit/s
Transfer parameters	CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)
Industrial communication Ethernet functionality	
duplex	Full duplex
Device protection Electrical	
Additional condition protection degree	inserted, screwed

Pollution Degree	3
Rated surge voltage	0.8 kV
Material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data Material data	
Material screw connection	Zinc die-casting
Coating of fitting	nickel plated
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	DIN EN 61076-2-113 (M12)
Installation Cable	
Function cable	Hybrid, Data, Power
Amount stranding	1
Stranding	Wires
Amount stranding (type 2)	1
Stranding (type 2)	Wires
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	85 %
Pair shielding (type)	copper braid, tinned
Pair shielding (coverage)	85 %
Banding	Fleece, Foil
Filler	yes
Wire arrangement	orange-white, green, orange, green-white, (, black, brown, white, blue,)
Cable weight	107.8
Material wire insulation	PP
Amount wires	4
Outer diameter insulation	1.5 mm
Outer diameter tolerance core insulation	± 0.1 mm
Shore hardness wire insulation	55
Ingredient freeness wire insulation	CFC-free, cadmium-free, silicone-free, halogen-free, lead-free
Amount strands (wire)	19
Diameter of single wires	32 AWG
Conductor crosssection (wire)	20 AWG
Material conductor wire	Stranded copper wire, bare
Material wire insulation (type 2)	PP
Outer diameter wire insulation (type 2)	1.1 mm
Tolerance outer diameter wire insulation (type 2)	± 0.1 mm
Shore hardness wire insulation (type 2)	55
Ingredient freeness wire insulation (type 2)	CFC-free, cadmium-free, silicone-free, halogen-free, lead-free
Amount wires (type 2)	4
Amount strands wire (type 2)	19
Diameter of single wires (type 2)	38 AWG
Conductor crosssection wire (type 2)	26 AWG

Material conductor wire (type 2)	Stranded copper wire, bare
Outer-diameter (jacket)	8.1 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PUR
Shore hardness jacket	90
Freedom from ingredients (jacket)	CFC-free, cadmium-free, silicone-free, halogen-free, lead-free
Material property (jacket)	matte, good machinability, abrasion-resistant, low adhesion
Conductor resistance (wire)	35 Ω/km
Conductor resistance (wire type 2)	140 Ω/km
Electrical capacity line constant (wire - wire)	52,000 pF/km
Isolation resistance	5,000 mΩ
Nominal voltage AC max.	60 V
Withstand voltage (wire - wire)	1 kV @ 60 s
Withstand voltage (wire - jacket)	1 kV @ 60 s
Withstand voltage (wire - shield)	1 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	7.2 A
Current load capacity min. Wire (type 2)	2.4 A
Characteristic impedance	100 Ω 15 %
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C / 90 °C @ 10000 h Operation
Operating temperature min. (dynamic)	-30 °C
Operating temperature max. (dynamic)	80 °C / 90 °C @ 10000 h Operation
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	5 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3.3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C
No. of torsion cycles	2 Mio.
Torsion stress	30 °/m
Torsion speed	35 cycles/min