

**M12 male recept. A-cod. rear**

PUR-wires 8x0.25 0.5m

Art.No.: 7000-17165-9730050

Weight: 0.034 kg

Country of origin: DE





Model designation: MSAFH-08D973\_0.5


Flange male

M12, 8-pole

Rear mounting

with multi-strand wire

[Link to Product](#)
**Illustration**




Product may differ from Image

**Header**

Cable length 0,50 m

**Side 1**

Family construction form M12

No. of poles 8

Coding A

Mounting method inserted, screwed

Threaded hole M12 x 1

Tightening torque 0,6 Nm

Width across flats SW14

Material Brass

Material contact Copper alloy

Coating contact gold plated

Degree of protection (EN IEC 60529) IP67

**Commercial data**URL Webshop <https://shop.murrelektronik.com/7000-17165-9730050>

customs tariff number 85444290

EAN 4048879331906

Packaging unit 1

**Electrical data | Supply**

Operating voltage AC max. 30 V

Operating voltage DC max. 30 V

Current operating per contact max. 2 A

**Diagnostics**

Status indication LED No

**Installation | Connection**

Mounting set M16 x 1.5

Width across flats SW19

**Device protection | Electrical**

Degree of protection (EN IEC 60529) IP67

Protection NEMA 6P, 4, 3

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I
<b>Mechanical data</b>	
Contour for corrugated hose	without
<b>Mechanical data   Material data</b>	
Material housing	Zinc die-casting
Coating housing	nickel plated
Material screw connection	Brass
Coating of fitting	nickel plated
Locking material	Brass
Coating locking	nickel plated
<b>Mechanical data   Mounting data</b>	
Mounting method	Schraubgewinde
Looking techniques	Schraubgewinde
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
<b>Important installation notes</b>	
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
<b>Conformity</b>	
Product standard	EN IEC 61076-2-101 (M12)
<b>Approvals</b>	
UL 50E	Yes
<b>Installation   Cable</b>	
Cable identification	973
Cable weight	48 g/m
Material wire insulation	PUR
Amount wires	8
Outer diameter insulation	1,25 mm
Amount strands (wire)	32
Diameter of single wires	0,1 mm
Conductor crosssection (wire)	0,25 mm <sup>2</sup>
Conductor type (wire)	strand class 6
Operating temperature min. (static)	-40 °C
Operating temperature max. (static)	90 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	90 °C
Bending radius (fixed)	10 × Outer diameter