

**Adaptor M12 male on top / MSUD valve plug A-18mm**

3-pol. A-cod.

Art.No.: 7000-41301-0000000

Weight: 0.035

Country of origin: CZ

Model designation: MSKL3-A

Form A (18 mm) – M12, connector top entry




24 V AC  $\pm 20\%$  / DC  $\pm 25\%$ 


LED and suppression

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Side 1	
Family construction form	MSUD
Tightening torque	0.4 Nm
Side 2	
Family construction form	M12
Tightening torque	0.6 Nm
Commercial data	
URL Webshop	<a href="https://shop.murrelektronik.com/7000-41301-0000000">https://shop.murrelektronik.com/7000-41301-0000000</a>
EAN	4048879144704
Electrical data   Supply	
Operating voltage AC	24 V
Operating voltage AC min.	19.2 V
Operating voltage AC max.	28.8 V
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	yellow
Installation   Connection	
Mounting set	M3
Installation   Pin assignment	
No. of poles	PE
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Rated surge voltage	0.8 kV
Material group (IEC 60664-1)	I
Environmental characteristics   Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C

Important installation notes

Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.