

Adaptor M12 male / M8 female A-cod.

3-pol., conf. 1,3,4

Art.No.: 7000-42201-0000000

Weight: 0.013 kg

Country of origin: DE

Model designation: MSF04L0-A-R




Adapter


Male - female

M12 – M8, 3-pole

for M12 distribution box, 3-pole

Art-No. 7005 - M12/M8 Lite - (plastic hexagonal screw) on request

[Link to Product](#)**Illustration**



Product may differ from Image

**Side 1**

Family construction form	M12
No. of poles	3
Coding	A
Threaded hole	M12 x 1
Tightening torque	0,6 Nm
Width across flats	SW13

Side 2

Family construction form	M8
No. of poles	3
Coding	A
Threaded hole	M8 x 1
Tightening torque	0,4 Nm
Width across flats	SW9

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-42201-0000000
customs tariff number	85366990
EAN	4048879143202
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	50 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	30 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Material group (IEC 60664-1)	I

Mechanical data | Material data

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-12-15

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Material housing	PUR
Locking material	Zinc die-casting
Coating locking	Nickeled
Mechanical data Mounting data	
Mounting method	Schraubgewinde
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Conformity	
Product standard	EN IEC 61076-2-101 (M12), EN IEC 61076-2-114 (M8)