



M12-PANEL FEED THROUGH 5 POLE B-CODED

Art.No.: 7000-44111-0000000
Weight: 0.027
Country of origin: CZ
Model designation: MSBBSV-BA-U


Control cabinet entry system
Male - female
M12, 5-pole
B-coded
shielded

Link to Product

Illustration



Product may differ from Image



| Side 1 | |
|--------------------------|----------|
| Family construction form | M12 |
| Coding | B |
| Side 2 | |
| Family construction form | M12 |
| Coding | B |
| Commercial data | |
| ECLASS-6.0 | 27279220 |

| | |
|-----------------------|---------------|
| ECLASS-6.1 | 27279220 |
| ECLASS-7.0 | 27440103 |
| ECLASS-8.0 | 27440103 |
| ECLASS-9.0 | 27440109 |
| ECLASS-10.1 | 27440109 |
| ECLASS-11.1 | 27440109 |
| ECLASS-12.0 | 27440109 |
| ETIM-5.0 | EC001855 |
| customs tariff number | 85366990 |
| customs tariff number | 85366990 |
| GTIN | 4048879141420 |
| GTIN | 4048879141420 |
| Packaging unit | 1 |
| Packaging unit | 1 |

Electrical data | Supply

| | |
|------------------------------------|------|
| Operating voltage AC max. | 60 V |
| Operating voltage DC max. | 60 V |
| Current operating per contact max. | 4 A |

Installation | Connection

| | |
|-------------------|-----------|
| Tightening torque | 0,6 Nm |
| Mounting set | M16 x 1.5 |

Device protection | Electrical

| | |
|--|-------------------|
| Degree of protection (EN IEC 60529) | IP65, IP67 |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree | 2 |
| Rated surge voltage | 1,5 kV |
| Material group (IEC 60664-1) | I |

Mechanical data | Material data

| | |
|------------------|---------------|
| Material housing | Brass |
| Coating housing | nickel plated |

Mechanical data | Mounting data

| | |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -25 °C |
| Operating temperature max. | 85 °C |

Important installation notes

| | |
|------------------------|---|
| Note on strain relief | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties. |
| Note on bending radius | Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |