

**M12 male 0° / M12 female 0° Y-cod. shielded**

PUR AWG20/26 shielded gn UL/CSA+drag ch. 7.5m

Art.No.: 7000-47051-8310750

Weight: 0.84

Country of origin: CZ

Model designation: MSYBL0-YA-08D831\_7.5-ZS

Ethernet CAT5

Male straight – female straight

M12 – M12, 8-pole

Y-coded




shielded



Transmission properties with channel transmission up to 50 m

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)****Illustration**



Product may differ from Image



Header	
Material short text	MSYBL0-YA-08D831_7.5-ZS
Cable length	7.5 m
Side 1	
Family construction form	M12
No. of poles	8
Coding	Y
Gender	male
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW13
Cable outlet	straight
Material	PUR
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP65, IP66K, IP67
Side 2	

Family construction form	M12
No. of poles	8
Coding	Y
Gender	female
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW13
Cable outlet	straight
Material	PUR
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP65, IP66K, IP67

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/7000-47051-8310750">https://shop.murrelektronik.com/7000-47051-8310750</a>
GTIN	4048879771580
ECLASS-6.0	27061801
ECLASS-6.1	27060307
ECLASS-7.0	27060307
ECLASS-7.1	27060307
ECLASS-8.0	27060307
ECLASS-8.1	27060307
ECLASS-9.0	27060307
ECLASS-9.1	27060307
ECLASS-10.0.1	27060307
ECLASS-10.1	27060307
ECLASS-11.0	27060307
ECLASS-11.1	27060307
ECLASS-12.0	27060307
ECLASS-13.0	27060307
ECLASS-14.0	27060307
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879771580
Packaging unit	1

#### Electrical data | Supply

Operating voltage AC max.	50 V
Operating voltage DC max.	50 V
Operating current per data contact max.	0.5 A
Operating current per power contact max.	6 A

#### Industrial communication

Data transmission rate max.	100 Mbit/s
Transfer parameters	CAT5e, Class D (ISO/IEC 11801)

#### Industrial communication | Ethernet functionality

duplex	Full duplex
--------	-------------

#### Device protection | Electrical

Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	0.8 kV

Material group (IEC 60664-1)

I

**Mechanical data**

Contour for corrugated hose without

**Mechanical data | Material data**

Material screw connection Zinc die-casting

Coating of fitting nickel plated

Material gasket FKM

**Environmental characteristics | Climatic**

Operating temperature min. -30 °C

Operating temperature max. 85 °C

Additional condition temperature range depending on cable quality

**Important installation notes**

Note on bending radius **Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Note on strain relief Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

**Conformity**

Product standard DIN EN 61076-2-113 (M12)

**Installation | Cable**

Function cable Hybrid, Data, Power

Amount stranding 1

Stranding Wires

Amount stranding (type 2) 1

Stranding (type 2) Wires

Cable shielding (type) copper braid, tinned

Cable shielding (coverage) 85 %

Pair shielding (type) copper braid, tinned

Pair shielding (coverage) 85 %

Banding Fleece, Foil

Wire arrangement (, black, brown, white, blue, ), orange-white, orange, green-white, green

Cable weight 107.8 g/m

Material wire insulation PP

Amount wires 4

Outer diameter insulation 1.5 mm

Outer diameter tolerance core insulation  $\pm 0.1$  mm

Shore hardness wire insulation 55

Ingredient freeness wire insulation CFC-free, cadmium-free, silicone-free, halogen-free, lead-free

Amount strands (wire) 19

Diameter of single wires 32 AWG

Conductor crosssection (wire) 20 AWG

Material conductor wire Stranded copper wire, bare

Material wire insulation (type 2) PP

Outer diameter wire insulation (type 2) 1.25 mm

Tolerance outer diameter wire insulation (type 2)  $\pm 0.1$  mm

Shore hardness wire insulation (type 2) 55

Ingredient freeness wire insulation (type 2) CFC-free, cadmium-free, silicone-free, halogen-free, lead-free

Amount wires (type 2) 4

Amount strands wire (type 2) 19

Diameter of single wires (type 2) 38 AWG

Conductor crosssection wire (type 2) 26 AWG

Material conductor wire (type 2) Stranded copper wire, bare

Outer-diameter (jacket) 8.1 mm

Tolerance outer diameter (sheath)  $\pm 5$  %

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-09-19

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Material jacket	PUR
Shore hardness jacket	90
Freedom from ingredients (jacket)	CFC-free, cadmium-free, silicone-free, halogen-free, lead-free
Material property (jacket)	matte, good machinability, abrasion-resistant, low adhesion
Conductor resistance (wire)	35 Ω/km
Conductor resistance (wire type 2)	140 Ω/km @ 20 °C
Electrical capacity line constant (wire - wire)	52,000 pF/km
Isolation resistance	5,000 MΩ × km
Nominal voltage AC max.	60 V
Withstand voltage (wire - wire)	1 kV @ 60 s
Withstand voltage (wire - jacket)	1 kV @ 60 s
Withstand voltage (wire - shield)	1 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. Wire (type 2)	2.4 A
Current carrying capacity min. wire (type 3)	7.2 A
Characteristic impedance	100 Ω 15 MHz
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C / 90 °C @ 10000 h Operation
Operating temperature min. (dynamic)	-30 °C
Operating temperature max. (dynamic)	80 °C / 90 °C @ 10000 h Operation
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	5 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3.3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C
No. of torsion cycles	2 Mio.
Torsion stress	30 °C
Torsion speed	35 cycles/min