

M12 male 0° / M12 female 0° Y-cod. shielded




PUR AWG20/26 shielded gn UL/CSA+drag ch. 1.5m



Art.No.: 7000-47051-8310150

Weight: 0.178

Country of origin: DE

Model designation: MSYBL0-YA-08D831_1.5-ZS

Link to Product**Illustration**



Product may differ from Image



1

| Header | |
|-------------------------------------|-------------------|
| Cable length | 1.5 m |
| Side 1 | |
| Family construction form | M12 |
| No. of poles | 8 |
| Coding | Y |
| Gender | male |
| Mounting method | inserted, screwed |
| Thread | M12 x 1 |
| Tightening torque | 0.6 Nm |
| Width across flats | SW13 |
| Cable outlet | straight |
| Material | PUR |
| Material contact | Copper alloy |
| Coating contact | gold plated |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |
| Side 2 | |
| Family construction form | M12 |

| | |
|-------------------------------------|-------------------|
| No. of poles | 8 |
| Coding | Y |
| Gender | female |
| Mounting method | inserted, screwed |
| Thread | M12 x 1 |
| Tightening torque | 0.6 Nm |
| Width across flats | SW13 |
| Cable outlet | straight |
| Material | PUR |
| Material contact | Copper alloy |
| Coating contact | gold plated |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

Commercial data

| | |
|---------------|---|
| URL Webshop | https://shop.murrelektronik.com/7000-47051-8310150 |
| GTIN | 4048879655606 |
| ECLASS-6.0 | 27061801 |
| ECLASS-6.1 | 27060307 |
| ECLASS-7.0 | 27060307 |
| ECLASS-7.1 | 27060307 |
| ECLASS-8.0 | 27060307 |
| ECLASS-8.1 | 27060307 |
| ECLASS-9.0 | 27060307 |
| ECLASS-9.1 | 27060307 |
| ECLASS-10.0.1 | 27060307 |
| ECLASS-10.1 | 27060307 |
| ECLASS-11.0 | 27060307 |
| ECLASS-11.1 | 27060307 |
| ECLASS-12.0 | 27060307 |
| ECLASS-13.0 | 27060307 |
| ECLASS-14.0 | 27060307 |
| ETIM-5.0 | EC001855 |
| ETIM-6.0 | EC001855 |
| ETIM-7.0 | EC001855 |
| ETIM-8.0 | EC001855 |
| EAN | 4048879655606 |

Electrical data | Supply

| | |
|--|-------|
| Operating voltage AC max. | 50 V |
| Operating voltage DC max. | 50 V |
| Operating current per data contact max. | 0.5 A |
| Operating current per power contact max. | 6 A |

Industrial communication

| | |
|-----------------------------|--------------------------------|
| Data transmission rate max. | 100 MBit/s |
| Transfer parameters | CAT5e, Class D (ISO/IEC 11801) |

Industrial communication | Ethernet functionality

| | |
|--------|-------------|
| duplex | Full duplex |
|--------|-------------|

Device protection | Electrical

| | |
|--|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree | 3 |
| Rated surge voltage | 0.8 kV |
| Material group (IEC 60664-1) | I |

Mechanical data

| | |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

| Mechanical data Material data | |
|---|---|
| Material screw connection | Zinc die-casting |
| Coating of fitting | nickel plated |
| Material gasket | FKM |
| Environmental characteristics Climatic | |
| Operating temperature min. | -30 °C |
| Operating temperature max. | 85 °C |
| Additional condition temperature range | depending on cable quality |
| Important installation notes | |
| Note on bending radius | Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Note on strain relief | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties. |
| Conformity | |
| Product standard | DIN EN 61076-2-113 (M12) |
| Installation Cable | |
| Function cable | Hybrid, Data, Power |
| Amount stranding | 1 |
| Stranding | Wires |
| Amount stranding (type 2) | 1 |
| Stranding (type 2) | Wires |
| Cable shielding (type) | copper braid, tinned |
| Cable shielding (coverage) | 85 % |
| Pair shielding (type) | copper braid, tinned |
| Pair shielding (coverage) | 85 % |
| Banding | Fleece, Foil |
| Wire arrangement | (, black, brown, white, blue,), orange-white, orange, green-white, green |
| Cable weight | 107.8 |
| Material wire insulation | PP |
| Amount wires | 4 |
| Outer diameter insulation | 1.5 mm |
| Outer diameter tolerance core insulation | ± 0.1 mm |
| Shore hardness wire insulation | 55 |
| Ingredient freeness wire insulation | CFC-free, cadmium-free, silicone-free, halogen-free, lead-free |
| Amount strands (wire) | 19 |
| Diameter of single wires | 32 AWG |
| Conductor crosssection (wire) | 20 AWG |
| Material conductor wire | Stranded copper wire, bare |
| Material wire insulation (type 2) | PP |
| Outer diameter wire insulation (type 2) | 1.1 mm |
| Tolerance outer diameter wire insulation (type 2) | ± 0.1 mm |
| Shore hardness wire insulation (type 2) | 55 |
| Ingredient freeness wire insulation (type 2) | CFC-free, cadmium-free, silicone-free, halogen-free, lead-free |
| Amount wires (type 2) | 4 |
| Amount strands wire (type 2) | 19 |
| Diameter of single wires (type 2) | 38 AWG |
| Conductor crosssection wire (type 2) | 26 AWG |
| Material conductor wire (type 2) | Stranded copper wire, bare |
| Outer-diameter (jacket) | 8.1 mm |
| Tolerance outer diameter (sheath) | ± 5 % |
| Material jacket | PUR |
| Shore hardness jacket | 90 |
| Freedom from ingredients (jacket) | CFC-free, cadmium-free, silicone-free, halogen-free, lead-free |

| | |
|---|---|
| Material property (jacket) | matte, good machinability, abrasion-resistant, low adhesion |
| Conductor resistance (wire) | 35 Ω /km |
| Conductor resistance (wire type 2) | 140 Ω /km @ 20 °C |
| Electrical capacity line constant (wire - wire) | 52,000 pF/km |
| Isolation resistance | 5,000 M Ω × km |
| Nominal voltage AC max. | 60 V |
| Withstand voltage (wire - wire) | 1 kV @ 60 s |
| Withstand voltage (wire - jacket) | 1 kV @ 60 s |
| Withstand voltage (wire - shield) | 1 kV @ 60 s |
| Current load capacity (standard) | to DIN VDE 0298-4 |
| Current load capacity min. Wire (type 2) | 2.4 A |
| Current carrying capacity min. wire (type 3) | 7.2 A |
| Characteristic impedance | 100 Ω 15 % |
| Min. operating temperature (static) | -40 °C |
| Max. operating temperature (fixed) | 80 °C / 90 °C @ 10000 h Operation |
| Operating temperature min. (dynamic) | -30 °C |
| Operating temperature max. (dynamic) | 80 °C / 90 °C @ 10000 h Operation |
| Bending radius (fixed) | 5 × Outer diameter |
| Bending radius (dynamic) | 10 × Outer diameter |
| No. of bending cycles (C-track) | 5 Mio. @ 25 °C |
| Traversing distance (C-track) | 5 m @ 25 °C |
| Travel speed (C-track) | 3.3 m/s @ 25 °C |
| Acceleration (C-track) | 5 m/s ² @ 25 °C |
| No. of torsion cycles | 2 Mio. |
| Torsion stress | 30 °/m |
| Torsion speed | 35 cycles/min |