

Adaptor M12 female 0° X-cod. / RJ45 0°

8-pol., shielded, CAT6A

Art.No.: 7000-51531-0000000

Weight: 0.048 kg

Country of origin: RO

Model designation: Adapter M12 X-Cod. auf RJ45 gerade

Adapter

M12 – RJ45

Female straight – female straight

8-pole




X-coded

Gigabit

Ethernet CAT6A

Shielded

Cap nut

[Link to Product](#)
Illustration


Product may differ from Image

Header

Material short text

Adapter M12 X-Cod. auf RJ45 gerade

Side 1

Family construction form	M12
No. of poles	8
Coding	X
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
Width across flats	SW18
Side 2	
Family construction form	RJ45
No. of poles	8
Mounting method	inserted
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-51531-0000000
GTIN	4048879699402
ECLASS-6.0	27143423
ECLASS-6.1	27279221
ECLASS-7.0	27440104
ECLASS-7.1	27440104
ECLASS-8.0	27440104
ECLASS-8.1	27440104
ECLASS-9.0	27440106
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440106
ECLASS-11.0	27440106
ECLASS-11.1	27440106
ECLASS-12.0	27440106
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002640
ETIM-6.0	EC002640
ETIM-7.0	EC002640
ETIM-8.0	EC002640
customs tariff number	85366990
EAN	4048879699402
Packaging unit	1
Electrical data Supply	
Operating current max.	1,75 A
Industrial Communication	
Supported protocol	Ethernet
Transfer parameters	CAT6A
Diagnostics	
Status indication LED	No
Installation Connection	
Width across flats	SW18
Device protection	
Shielded	Yes
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.