

## MSUD double valve A-18mm with cable

PVC 4x0.75 ye 5m

Art.No.: 7000-58021-0170500

Weight: 0.355 Country of origin: CZ

Model designation: MSKL3-016\_150-KL3-017\_5.0

Form A (18 mm) 24 V AC ±20% / DC ±25% LED and suppression Connection cable L = 150 mm Further cable lengths on request.


Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


## **Link to Product**

## Illustration











Product may differ from Image

33

Height: 30 mm

43.5



Cable length	5 m	
Side 1		
Tightening torque	0,4 Nm	
Thread	M3	
Side 2		
Tightening torque	0,4 Nm	
Thread	M3	
Commercial data		
ECLASS-6.0	27279218	
ECLASS-6.1	27279218	
ECLASS-7.0	27279218	
ECLASS-8.0	27279218	
ECLASS-9.0	27060312	
ECLASS-10.1	27060312	
ECLASS-11.1	27060312	
ECLASS-12.0	27060312	
ETIM-5.0	EC001855	
customs tariff number	85444290	
customs tariff number	85444290	
EAN	4048879137621	
EAN	4048879137621	
Packaging unit	1	
Packaging unit	1	
Electrical data		
Drop-out delay time max.	20 ms	
Electrical data   Supply		
Operating voltage AC	24 V	
Operating voltage AC min.	19,2 V	
Operating voltage AC max.	28,8 V	
Operating voltage DC	24 V	
Operating voltage DC min.	18 V	
Operating voltage DC max.	30 V	

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-05



stay connected

Cut-off peak voltage max.	55 V
Current operating per contact max.	4 A
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Rated surge voltage	0,8 kV
Mechanical data   Material data	
Material housing	Plastic
Color housing	black
· ·	Diadri
Mechanical data   Mounting data	
Mounting method	inserted, screwed
Environmental characteristics   Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Installation   Cable	
wire arrangement	black 1, black 2, black 3, green-yellow
Cable identification	017
Cable Type	1
Printing color of wire insulation	white (isolation black)
Jacket Color	yellow
Amount stranding	1
Stranding	4 wires twisted
wire arrangement	black 1, black 2, black 3, green-yellow
Cable weigth	81,4 g/m
Material jacket	PVC
Shore hardness jacket	80 ± 5 Shore A
Freedom from ingredients (jacket)	lead-free, cadmium-free, CFC-free, silicone-free
Outer-diameter (jacket)	6,5 mm
Tolerance outer diameter (sheath)	±5%
Material wire insulation	PVC
Amount wires	4
Outer diameter insulation	1,8 mm
Outer diameter tolerance core insulation	±5%
Shore hardness wire insulation	43 ± 5 Shore D
Material properties wire insulation	good machinability
Ingredient freeness wire insulation	lead-free, cadmium-free, CFC-free, silicone-free
Printing color of wire insulation	white (isolation black)
Amount strands (wire)	24
Diameter of single wires	0,2 mm
Conductor crosssection (wire)	0,75 mm²
Material conductor wire	Stranded copper wire, bare
Conductor type (wire)	Strand class 5
Max. rated voltage (conductor - conductor)	500 V
Max. rated voltage (conductor - ground)	300 V
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	9,6 A
Electrical resistance line constant wire	26 Ω/km @ 20 °C



AC withstand voltage (wire - wire)	3 kV @ 60 s
Power frequency withstand voltage (wire - jacket)	3 kV @ 60 s
Min. operating temperature (static)	-30 °C
Max. operating temperature (fixed)	70 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	70 °C
Flame resistance	UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090
chemical resistance	Good, application-related testing
Gasoline resistance	Good, application-related testing
Oil resistance	DIN EN 60811-404   Good, application-related testing
Bending radius (fixed)	5 x Outer diameter
Bending radius (dynamic)	10 x Outer diameter