

Adapter M12 male/ female B-cod. / D-Sub 9-pol. 90°

Shielded, 12Mbit/s

Art.No.: 7000-99411-0000000
Weight: 0.045
Country of origin: HU
Model designation: M12/D-Sub Profibus Adapter 90°


PROFIBUS
Bus connection plug 90°
SUB-D9 (male); M12× 1 mm, B-coded
Programming device

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27061801
ECLASS-7.0	27061801
ECLASS-8.0	27061801
ECLASS-9.0	27061801
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879303637
GTIN	4048879303637
Packaging unit	1
Packaging unit	1
Electrical data	
Terminating resistor	connectable, integrated
Electrical data Supply	
Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA
Industrial communication	

Data transmission rate max.	12 MBit/s
-----------------------------	-----------

Installation | Connection

Family construction form	M12
--------------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP30
-------------------------------------	------

Mechanical data | Mounting data

Height	59 mm
--------	-------

Width	45 mm
-------	-------

Depth	17 mm
-------	-------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	70 °C
----------------------------	-------

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
------------------------	---