

Cable drum Ø 355mm

PUR 1x4xAWG22 shielded gn UL/CSA+drag ch. 100m

Art.No.: 7000-C0201-7960000

Weight: 7.523 Country of origin: US

Model designation: 100m Kabel 10080605(796)gesch.Kabeltromm

Product fulfills requirements according to UN/ECE R118


Cable drum (100 m)

Ethernet CAT5, PROFINET IO, EtherCAT


2× 2× 0.34 mm² PUR (UL/CSA) suitable for C-tracks

Link to Product

Illustration







Product may differ from Image





Header

Material short text

100m Kabel 10080605(796)gesch.Kabeltromm



stay connected

	//
URL Webshop	https://shop.murrelektronik.com/7000-C0201-7960000
GTIN	4048879334501
ECLASS-6.0	27062011
ECLASS-6.1	27061801
ECLASS-7.0	27061801
ECLASS-7.1	27061801
ECLASS-8.0	27061801
ECLASS-8.1	27061801
ECLASS-9.0	27061801
ECLASS-9.1	27061801
ECLASS-10.0.1	27061801
ECLASS-10.1	27061801
ECLASS-11.0	27061801
ECLASS-11.1	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801
ECLASS-14.0	27061801
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444995
EAN	4048879334501
Packaging unit	1
Important installation notes	
	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be
Note on bending radius	endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Installation Cable	
Cable identification	796
Function cable	Data
Amount stranding	1
Stranding	4 wires around core filler star-shaped twisted
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	85 %
Banding	Foil, Fleece
Filler	yes
Cable weigth	63 g/m
Material wire insulation	PE
Amount wires	4
Outer diameter insulation	1.4 mm
Outer diameter tolerance core insulation	± 0.05 mm
Shore hardness wire insulation	65 ± 5 Shore D
Ingredient freeness wire insulation	lead-free, CFC-free, halogen-free
Amount strands (wire)	7
Diameter of single wires	30 AWG
Conductor crosssection (wire)	22 AWG
Material conductor wire	Stranded copper wire, bare
Outer-diameter (jacket)	6.7 mm
Tolerance outer diameter (sheath)	±5%
	PUR
Material jacket	
Shore hardness jacket Freedom from ingredients (jacket)	89 ± 5 Shore A lead-free, cadmium-free, CFC-free, halogen-free, silicone-free

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-04



Material property (jacket)	abrasion-resistant, low adhesion, good machinability, matte
Material inner jacket	FRNC
Color (inner jacket)	natural
Conductor resistance (wire)	55.4 Ω/km @ 20 °C
Electrical capacity line constant (wire - wire)	50,000 pF/km
Isolation resistance	5,000 MΩ × km
Nominal voltage AC max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - jacket)	2 kV @ 60 s
Withstand voltage (wire - shield)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	4.8 A
Characteristic impedance	100 Ω ± 15 %
Min. operating temperature (static)	-40 °C
Max. operating temperature (static)	80 °C
Operating temperature min. (dynamic)	-30 °C
Operating temperature max. (dynamic)	70 °C
Operating temperature min. (drag chain)	-30 °C
Operating temperature max. (drag chain)	70 °C
Flame resistance	UL 1581 § 1090, UL 1581 § 1100, IEC 60332-1-2
Oil resistance	IEC 60811-404, NEMA WC55, IRM 901
Ozone resistance	IEC 60811-403
UV resistance	UL 1581 § 1200
Other resistances	resistant to hydrolysis, resistant to microbes, MUD-resistant (NEK 606)
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	12 × Outer diameter
No. of bending cycles (C-track)	3 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3.3 m/s @ 25 °C
Acceleration (C-track)	2 m/s² @ 25 °C
No. of torsion cycles	1 Mio. @ 25 °C
Torsion stress	± 180 °/m
Torsion speed	35 cycles/min