

## M12 Power male recept. L-cod. front incl. nut

PUR-wires 5x1.5 0.5m

Art.No.: 7000-P4282-9800050

Weight: 0.111

Country of origin: DE

Model designation: MSWALFV-U980\_0.5

Power Flange male M12, 5-pole L-coded Front mounting

with multi-strand wire

Hexagon nut M16x1.5 (SW19) for flange connector included in the delivery package

Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)


The resistance to aggressive media should be individually tested for your application. Further details on request.


Further cable lengths on request.


## **Link to Product**

## Illustration










stay connected



Product may differ from Image









Header	
Material short text	MSWALFV-U980_0.5
Cable length	0,50 m
Side 1	
Family construction form	M12P
No. of poles	5
Coding	L
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW17
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP65, IP67, IP69K
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-P4282-9800050
GTIN	4048879809979
ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440103
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440103
ECLASS-11.0	27440109
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440109
ECLASS-14.0	27440109
ETIM-5.0	EC002061
ETIM-6.0	EC002061

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-05



stay connected

customs tariff number	85444290
EAN	4048879809979
Packaging unit	1
Electrical data   Supply	
Operating voltage DC max.	63 V
Current operating per contact max.	12 A
Diagnostics	
Status indication LED	no
Installation   Connection	
Mounting set	M16 x 1.5
Width across flats	SW19
	OW15
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67, IP65
Protection NEMA	6P, 4, 3
Additional condition protection degree	mounted, screwed
Pollution Degree Rated surge voltage	3 1.5 kV
Material group (IEC 60664-1)	1.5 KV
Mechanical data	
	. Maria
Contour for corrugated hose	without
Mechanical data   Material data	
Material housing	Brass
Coating housing	nickel plated
Locking material	Brass
Coating locking	nickel plated
Mechanical data   Mounting data	
Mounting method	inserted, screwed
Environmental characteristics   Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	EN IEC 61076-2-111
Approvals	
UL 50E	yes
Temperature range   Cable	,
	000
Cable identification  Cable weigth	980 97.5 a/m
Material wire insulation	97.5 g/m PUR
Amount wires	5
Outer diameter insulation	2.4 mm
Amount strands (wire)	
	30
Diameter of single wires	0.25 mm
Conductor crosssection (wire)	1.5 mm <sup>2</sup>
Material conductor wire	copper stranded wire, tinned



Conductor type (wire)	Strand class 5
Min. operating temperature (static)	-40 °C
Max. operating temperature (static)	90 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	90 °C