

M12 Power female 0° L-cod. screw terminal5-pol., max. 2,5mm², 8 - 13mm

Art.No.: 7000-P4611-0000000

Weight: 0.055

Country of origin: DE

Model designation: MSWBL-U-SK max. 2.5mm²

Female straight

M12

5-pole



L-coded

Screw terminals


Sealing range (cable Ø)

8...13 mm

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-09-16

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Material short text	MSWBL-U-SK max. 2.5mm²
---------------------	------------------------

Side 1

Family construction form	M12P
No. of poles	5
Coding	L
Gender	female
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Cable outlet	straight
Material contact	Copper alloy

Side 2

Mounting method	field-wireable
-----------------	----------------

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-P4611-0000000
GTIN	4048879786560
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879786560
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	63 V
Operating voltage DC max.	63 V
Current operating per contact max.	16 A

Diagnostics

Status indication LED	no
-----------------------	----

Installation

Cross section connection with wire end ferrule max.	15 mm²
Cross section connection with wire end ferrule AWG max.	16 AWG
Cross section connection without wire end ferrule max.	25 mm²
Cross section connection without wire end ferrule AWG max.	14 AWG

AWG number max. 14

Installation | Connection

Connection	Screw terminals SK
Mounting set	M12 x 1
Mating cycles min.	100

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Overvoltage category (EN 60950-1)	III
Rated surge voltage	1.5 kV
Material group (IEC 60664-1)	II

Mechanical data | Material data

Material housing	PA
Material contact carrier	PA
Coating contact	gold plated

Mechanical data | Mounting data

Mounting method	Schraubgewinde
Clamping range min.	8 mm
Clamping range max.	13 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.