

MQ15-X-Power male receptacle front mount

wires PVC 4x2,5 0,5m

Art.No.: 7000-P8081-P820050

Weight: 0.065 Country of origin: DE

Model designation: MSWAQ3FV-P82 0.5

Flange male MQ15, 4-pole with multi-strand wire Front mounting

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.


Further cable lengths on request.


Hexagon nut M20x1,5 (SW26) for flange connector included in the delivery package.


Link to Product

Illustration













stay connected





Product may differ from Image







Header	
Material short text	MSWAQ3FV-P82_0.5
Cable length	0,50 m
Side 1	
Family construction form	MQ15
No. of poles	4
Coding	Type 3
Mounting method	inserted, screwed
Material contact	Copper alloy
Coating contact	silver-plated
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-P8081-P820050
GTIN	4065909027967
ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440103
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440103
ECLASS-11.0	27440109
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440109
ECLASS-14.0	27440109
ETIM-5.0	EC002061
ETIM-6.0	EC002061
customs tariff number	85444290
EAN	4065909027967
Packaging unit	1



stay connected

Electrical data Supply	
Operating voltage AC max.	600 V
Current operating per contact max.	16 A
Diagnostics	
Status indication LED	no
	110
Installation Connection	
Tightening torque	6 Nm
Mounting set	M20 x 1.5
Width across flats	SW22
Mating cycles min.	500
Installation Pin assignment	
Configuration	fully used
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	6 kV
Material group (IEC 60664-1)	
Mechanical data Material data	
·	Drana
Material housing	Brass
Coating housing Material contact carrier	nickel plated PA
	ra
Mechanical data Mounting data	
_ooking techniques	bayonet-locking
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	90 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	EN IEC 61076-2-116
Temperature range Cable	
Cable identification	P82
Material wire insulation	PVC
Amount wires	4
Outer diameter insulation	3.7 mm
Conductor crosssection (wire)	2.5 mm ²
Material conductor wire	copper stranded wire, tinned
Conductor type (wire)	Strand class 5
Nominal voltage AC max.	600 V
Withstand voltage (wire - wire)	2.5 kV
(AC) lead and a college of a dead and a lead of	2.5 kV
Withstand voltage (wire - jacket)	