


B16 female 4+2-pole, screw t., 830/400 V, 80/16 A

Art.No.: 70MH-EB4U2-FS04000
Weight: 0.113
Country of origin: CZ
Model designation: MSMH-EBU-B16-S-4+2pol. 830/400 V 80/16 A


B16
Female
4+2-pole
Screw terminal
Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440205
ECLASS-8.0	27440205
ECLASS-9.0	27440205
ECLASS-10.1	27440205
ECLASS-11.1	27440205
ECLASS-12.0	27440205
ETIM-5.0	EC000438
customs tariff number	85389099
customs tariff number	85389099
GTIN	4048879637404
GTIN	4048879637404
Packaging unit	1
Packaging unit	1

Electrical data | Supply

Operating voltage AC per power contact max.	830 V
Operating voltage AC per signal contact max.	400 V

Operating voltage DC per power contact max.	830 V
---	-------

Operating voltage DC per signal contact max.	400 V
--	-------

Operating current per power contact max.	80 A
--	------

Operating current per signal contact max.	16 A
---	------

Installation

Connection cross section min.	1,5 mm ²
-------------------------------	---------------------

Connection cross section max.	16 mm ²
-------------------------------	--------------------

AWG number min.	16
-----------------	----

AWG number max.	5
-----------------	---

Installation | Connection

Stripping length min.	6 mm
-----------------------	------

Stripping length max.	14 mm
-----------------------	-------

Wire insulation diameter variable max.	max. 11 mm (Power); max. 4.8 mm (Signal)
--	--

Connection	Screw terminals SK
------------	--------------------

Tightening torque	min. 2.5 Nm (Power); min. 0.5 Nm (Signal)
-------------------	---

Gender	female
--------	--------

Mating cycles min.	500
--------------------	-----

Installation | Pin assignment

No. of poles	4 + 2 + PE
--------------	------------

Device protection | Electrical

Pollution Degree	3
------------------	---

Rated surge voltage	8 kV
---------------------	------

Insulation resistance min.	100 MΩ
----------------------------	--------

Material group (IEC 60664-1)	IIIa
------------------------------	------

Overvoltage category (EN 60664-1)	III
-----------------------------------	-----

Overvoltage category (EN 60950-1)	III
-----------------------------------	-----

Mechanical data

Holding force power min.	500 N
--------------------------	-------

Holding force signal min.	400 N
---------------------------	-------

Pulling force max.	100 N
--------------------	-------

Mechanical data | Material data

Coating contact	silver-plated
-----------------	---------------

Combustibility class (UL94)	V-0
-----------------------------	-----

Material contact	Brass
------------------	-------

Material contact carrier	PC GF
--------------------------	-------

Mechanical data | Mounting data

Size	B16
------	-----

Height	42 mm
--------	-------

Width	33,8 mm
-------	---------

Depth	83,7 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	125 °C
----------------------------	--------

Climatic category (EN IEC 60068-1)	40/125/21
------------------------------------	-----------