

B6 frame (male) for 2 modules


A...B

Art.No.: 70MH-RD02S-0000000  
Weight: 0.054  
Country of origin: CZ  
Model designation: MSMH-RB06 ST-2Module-A...B


B6  
Frame  
Male  
for 2 modules  
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27143424      |
| ECLASS-6.1            | 27261209      |
| ECLASS-7.0            | 27440206      |
| ECLASS-8.0            | 27440206      |
| ECLASS-9.0            | 27440206      |
| ECLASS-10.1           | 27440206      |
| ECLASS-11.1           | 27440206      |
| ECLASS-12.0           | 27440206      |
| ETIM-5.0              | EC002312      |
| customs tariff number | 85389099      |
| customs tariff number | 85389099      |
| GTIN                  | 4048879641753 |
| GTIN                  | 4048879641753 |
| Packaging unit        | 1             |
| Packaging unit        | 1             |

Installation

|                               |       |
|-------------------------------|-------|
| Connection cross section min. | 1 mm² |
| Connection cross section max. | 6 mm² |
| AWG number min.               | 18    |
| AWG number max.               | 10    |

Installation | Connection

|                                                 |                    |
|-------------------------------------------------|--------------------|
| Connection                                      | Screw terminals SK |
| Insertion cycles safety element min.            | 20                 |
| Mating cycles min.                              | 500                |
| <b>Installation   Pin assignment</b>            |                    |
| No. of poles                                    | 2 + PE             |
| <b>Mechanical data</b>                          |                    |
| Holding force modules (insert) min.             | 300 N              |
| Holding force modules (pull) min.               | 600 N              |
| Holding force PE contact                        | 250 N              |
| Frame type                                      | male               |
| Pulling force max.                              | 60 N               |
| <b>Mechanical data   Material data</b>          |                    |
| Material housing                                | Zinc die-casting   |
| Coating housing                                 | nickel plated      |
| Coating contact                                 | nickel plated      |
| Combustibility class (UL94)                     | V-0                |
| Material contact                                | Brass              |
| Material safety element                         | PC GF              |
| <b>Mechanical data   Mounting data</b>          |                    |
| Number of module slots                          | 2                  |
| Size                                            | B6                 |
| Height                                          | 36,5 mm            |
| Width                                           | 34,4 mm            |
| Depth                                           | 51,2 mm            |
| <b>Environmental characteristics   Climatic</b> |                    |
| Operating temperature min.                      | -40 °C             |
| Operating temperature max.                      | 125 °C             |
| Climatic category (EN IEC 60068-1)              | 40/125/10          |