

Male module, 1-pole, axial screw t.

1000 V, 200 A
Art.No.: 70MH-MAB2A-0010707
Weight: 0.067
Country of origin: PL
Model designation: MSMH-MSTM-2M-A-1pol. 1000 V 200 A


Male
1-pole
Axial screw connection
Technical data will be only guaranteed with Murrelektronik components.
Axial screw connection only for flexible wires
The clip 70MH-ZZ100-0000000 is needed (4×)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440217
ECLASS-10.1	27440217
ECLASS-11.1	27440217
ECLASS-12.0	27440217
ETIM-5.0	EC000438
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879663922
GTIN	4048879663922
Packaging unit	1
Packaging unit	1
Electrical data Supply	

Operating voltage AC	1000 V
----------------------	--------

Operating voltage DC	1000 V
----------------------	--------

Operating current	200 A
-------------------	-------

Installation

Connection cross section min.	25 mm ²
-------------------------------	--------------------

Connection cross section max.	70 mm ²
-------------------------------	--------------------

AWG number min.	3
-----------------	---

AWG number max.	0
-----------------	---

Installation | Connection

Stripping length	16 mm
------------------	-------

Wire insulation diameter variable max.	max. 12 mm (25 mm ²); 16 mm (40 mm ²)
--	---

Connection information	Axial screw connection
------------------------	------------------------

Tightening torque	(25...35 mm ²); 9 Nm (50 mm ²); 10 Nm (70 mm ²)
-------------------	---

Tightening torque	8 Nm
-------------------	------

Gender	male
--------	------

Width across flats	SW5
--------------------	-----

Mating cycles min.	500
--------------------	-----

Installation | Pin assignment

No. of poles	1
--------------	---

Device protection | Electrical

Pollution Degree	3
------------------	---

Rated surge voltage	8 kV
---------------------	------

Overvoltage category (EN 60950-1)	III
-----------------------------------	-----

Mechanical data | Material data

Material housing	PC
------------------	----

Coating contact	silver-plated
-----------------	---------------

Combustibility class (UL94)	V-0
-----------------------------	-----

Material contact	Brass
------------------	-------

Mechanical data | Mounting data

Number of module slots	2
------------------------	---

Height	35 mm
--------	-------

Width	30,3 mm
-------	---------

Depth	29,4 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	125 °C
----------------------------	--------