

**PE-Male module, 1-pole, axial screw t.**

1000 V, 200 A

Art.No.: 70MH-MAQ2A-0010707

Weight: 0.093

Country of origin: PL

Model designation: MSMH-MSTM(PE)-2M-A-1pol. 1000 V 200 A

Male

PE

Axial screw connection


Technical data will be only guaranteed with Murrelektronik components.

Axial screw connection only for flexible wires

The clip 70MH-ZZ100-0000000 is needed (4×)

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27143424
ECLASS-7.0	27440209
ECLASS-8.0	27440209
ETIM-5.0	EC000438
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879663939
GTIN	4048879663939
Packaging unit	1
Packaging unit	1

**Electrical data | Supply**

Operating current	200 A
-------------------	-------

**Installation**

Connection cross section min.	25 mm <sup>2</sup>
Connection cross section max.	70 mm <sup>2</sup>
AWG number min.	3
AWG number max.	0

**Installation | Connection**

Stripping length	16 mm
------------------	-------

Wire insulation diameter variable max.	max. 12 mm (25 mm <sup>2</sup> ); 16 mm (40 mm <sup>2</sup> )
--	---

Connection information	Axial screw connection
Tightening torque	(25...70 mm <sup>2</sup> ); 9 Nm (70 mm <sup>2</sup> )
Tightening torque	8 Nm
Gender	male
Width across flats	SW5
Mating cycles min.	500

#### Installation | Pin assignment

No. of poles	PE
--------------	----

#### Device protection | Electrical

Pollution Degree	3
------------------	---

#### Mechanical data | Material data

Material housing	PC
Coating contact	silver-plated
Combustibility class (UL94)	V-0
Material contact	Brass

#### Mechanical data | Mounting data

Number of module slots	2
Height	61,1 mm
Width	34,3 mm
Depth	29,3 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	125 °C