

#### M12 male 0° / M12 male 0° D-cod. shielded

TPE 2x2x24AWG SF/UTP CAT5e bu UL/CSA. CM 7.5m

Art.No.: 7700-44511-S4U0750

Weight: 0.408 Country of origin: US

Model designation: MSDAL0-DA-TS4U 7.5-ZS

# Advantages of our connectors:

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.

The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available on request

If you are missing technical information? Please feel free to use our dictionary to find more technical details.

### **Product details:**

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request. USA

Ethernet CAT5

Male straight – male straight
M12 – M12, 4-pole
D-coded
shielded


without cable sleeves

maximum length at channel transmission corresponds to 70 m

### **Link to Product**


## Illustration









stay connected







Product may differ from Image













Cable length	7,5 m
Side 1	
Tightening torque	0,6 Nm
Mounting method	inserted, screwed
Family construction form	M12
Thread	M12 x 1
Cable outlet	straight
Coding	D
No. of poles	4
Width across flats	SW13
Side 2	
Tightening torque	0,6 Nm
Mounting method	inserted, screwed
Family construction form	M12
Thread	M12 x 1
Cable outlet	straight
Coding	D
No. of poles	4

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-05



stay connected

Width across flats	SW13
Commercial data	
ECLASS-6.0	27061801
ECLASS-6.1	27060307
ECLASS-7.0	27060307
ECLASS-8.0	27060307
ECLASS-9.0	27060307
ECLASS-10.1	27060307
ECLASS-11.1	27060307
ECLASS-12.0	27060307
ETIM-5.0	EC002599
customs tariff number	85444290
customs tariff number	85444290
EAN	4048879605885
EAN	4048879605885
Packaging unit	1
Packaging unit	1
Electrical data   Supply	
Operating voltage DC max.	60 V
Current operating per contact (UL)	1,5 A
Current operating per contact max.	1,5 A
Industrial communication	
Transfer parameters	CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)
Data transmission rate max.	100 MBit/s
Industrial communication   Ethernet fun	octionality
duplex	Full duplex
·	Tull duplex
Diagnostics	
Status indication LED	no
Installation   Connection	
Gender	male
•	male
Gender	male IP65, IP67, IP66K
Gender  Device protection   Electrical	
Gender  Device protection   Electrical  Degree of protection (EN IEC 60529)	IP65, IP67, IP66K
Gender  Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree	IP65, IP67, IP66K inserted, screwed
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage	IP65, IP67, IP66K inserted, screwed 3
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage	IP65, IP67, IP66K inserted, screwed 3
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data	IP65, IP67, IP66K inserted, screwed 3
Gender  Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)	IP65, IP67, IP66K inserted, screwed 3 1,5 kV
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data	IP65, IP67, IP66K inserted, screwed 3 1,5 kV I
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing	IP65, IP67, IP66K inserted, screwed 3 1,5 kV
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking	IP65, IP67, IP66K inserted, screwed 3 1,5 kV I without PUR Nickeled
Gender  Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material	IP65, IP67, IP66K inserted, screwed 3 1,5 kV I without
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material  Mechanical data   Mounting data	IP65, IP67, IP66K inserted, screwed 3 1,5 kV I without  PUR Nickeled Zinc die-casting
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material  Mechanical data   Mounting data  Mounting method	IP65, IP67, IP66K inserted, screwed  3 1,5 kV I without  PUR Nickeled Zinc die-casting inserted, screwed, Shaking protection
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material  Mechanical data   Mounting data  Mounting method  Environmental characteristics   Climatic	IP65, IP67, IP66K inserted, screwed 3 1,5 kV I without  PUR Nickeled Zinc die-casting inserted, screwed, Shaking protection
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material  Mechanical data   Mounting data  Mounting method  Environmental characteristics   Climatic	IP65, IP67, IP66K inserted, screwed  3 1,5 kV I without  PUR Nickeled Zinc die-casting inserted, screwed, Shaking protection
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material  Mechanical data   Mounting data  Mounting method  Environmental characteristics   Climatic  Operating temperature min.	IP65, IP67, IP66K inserted, screwed  3 1,5 kV I without  PUR Nickeled Zinc die-casting inserted, screwed, Shaking protection  -25 °C 85 °C
Device protection   Electrical  Degree of protection (EN IEC 60529)  Additional condition protection degree  Pollution Degree  Rated surge voltage  Material group (IEC 60664-1)  Mechanical data  Contour for corrugated hose  Mechanical data   Material data  Material housing  Coating locking  Locking material  Mechanical data   Mounting data  Mounting method  Environmental characteristics   Climatic  Operating temperature min.	IP65, IP67, IP66K inserted, screwed  3 1,5 kV I without  PUR Nickeled Zinc die-casting inserted, screwed, Shaking protection



stay connected

	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Conformity	
Product standard	DIN EN 61076-2-101 (M12)
Installation   Cable	
wire arrangement	(orange-white, orange), (green-white, green)
Cable identification	S4U
Function cable	Data
Jacket Color	teal
Type of Certificate	cURus
Amount stranding	2
Stranding	2 wires twisted
Amount stranding (type 2)	1
Stranding (type 2)	2 Stranded joints twisted
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	75 %
Banding	Foil
vire arrangement	(orange-white, orange), (green-white, green)
Cable length max.	(orange-write, orange), (green-write, green)
Cable weigth	
	55,66 g/m TPE
Material jacket	
Freedom from ingredients (jacket)	lead-free, CFC-free
Outer-diameter (jacket)	6,6 mm
Tolerance outer diameter (sheath)	±5%
Material wire insulation	HDPE
Amount wires	4
Outer diameter insulation	1,22 mm
Outer diameter tolerance core insulation	±5%
ngredient freeness wire insulation	lead-free, CFC-free
Amount strands (wire)	7
Diameter of single wires	24 AWG
Conductor crosssection (wire)	24 AWG
Material conductor wire	copper stranded wire, tinned
Nominal voltage AC max.	600 V
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	2,4 A
Characteristic impedance	100 Ω @ 100 MHz
Electrical resistance line constant wire	76,4 Ω/km @ 20 °C
AC withstand voltage (wire - wire)	1,5 kV @ 2 s
Power frequency withstand voltage (wire - acket)	1,5 kV @ 2 s
oop resistance	280 Ω/km
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C
Operating temperature min. (dynamic)	-40 °C
Operating temperature max. (dynamic)	80 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Flame resistance	UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2
chemical resistance	Good, application-related testing
Gasoline resistance	Good, application-related testing
Oil resistance	DIN EN 60811-404   Good, application-related testing
Bending radius (fixed)	8 x Outer diameter



Bending radius (dynamic)	8 x Outer diameter
No. of bending cycles (C-track)	35 Mio.
Traversing distance (C-track)	0,6 m
Travel speed (C-track)	1,2 m/s
No. of torsion cycles	3 Mio.
Torsion stress	± 270 °/m
Torsion speed	60 cycles/min