

EXACT8, 4XM8, 3 POLE

Conn.M12 12 pole

Art.No.: 8000-84060-0000000

Weight: 0.101 kg

Country of origin: DE

Model designation: MVP8N-GS4D




4-way, 3-pole


M12 (12-pole)

Inline face or side mounting

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Header	
Material short text	MVP8N-GS4D
Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-84060-0000000
GTIN	4048879056311
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879056311
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Current operating per contact max.	1,5 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	mounted, screwed

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	70 °C
Additional condition temperature range	depending on cable quality

Connection type 2

Family construction form	M12
No. of poles	12
Coding	A
Gender	male
Color contact carrier	black
PIN 1	BN
PIN 2	BU
PIN 3	WH
PIN 4	GN
PIN 5	PK
PIN 6	YE
PIN 7	BK
PIN 8	GY
PIN 9	RD
PIN 10	VT
PIN 11	GY / PK
PIN 12	RD / BU
Family construction form	M8
No. of poles	3
Coding	A
Gender	female
Color contact carrier	black
PIN 1	24 V DC
PIN 3	0 V
PIN 4	S