

EXACT12, 4XM12, 5-POLE, BASIC HOUSING

Without homerun-cable

Art.No.: 8000-84500-0000000

Weight: 0.078 kg

Country of origin: DE

Model designation: MVP12N-MN4F

4-way, 5-pole

Form PNP




Screw plug-in terminals



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration





Product may differ from Image



Header

Material short text MVP12N-MN4F

Commercial data

URL Webshop	https://shop.murrelektronik.com/8000-84500-0000000
GTIN	4048879055857
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879055857
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current max.	8 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP65
-------------------------------------	------------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	70 °C
----------------------------	-------

Connection type 2

Family construction form	Cap
--------------------------	-----

No. of poles	12
--------------	----

Family construction form	M12
--------------------------	-----

No. of poles	5
--------------	---

Coding	A
--------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

PIN 1	+
-------	---

PIN 2	NC S 2
-------	--------

PIN 3	-
-------	---

PIN 4	NO S 1
-------	--------

PIN 5	PE
-------	----