

## EXACT12, 4XM12, 5 POLE

Conn.M12 12pole

Art.No.: 8000-84560-0000000

Weight: 0.105 Country of origin: DE

Model designation: MVP12N-GS4F

4-way, 5-pole M12 plug connection 12-pole used

with LED for digital PNP-signals 24 V DC


Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


## **Link to Product**

## Illustration













stay connected





Product may differ from Image









Tieduci	
Material short text	MVP12N-GS4F
Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-84560-0000000
GTIN	4048879296328
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879296328
Packaging unit	1
Electrical data   Supply	
Operating voltage DC	24 V
Current operating per contact max.	1.5 A
Total current max.	1.5 A
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67, IP65

Color contact carrier



Davisa nustration   Madia	
Device protection   Media	
Flame resistance	flame retardant
Mechanical data   Material data	
Material housing	Plastic
Environmental characteristics   Clima	tic
Operating temperature min.	-20 °C
Operating temperature max.	70 °C
Connection type 2	
Family construction form	M12
No. of poles	5
Coding	Α
Gender	female
Color contact carrier	black
PIN 1	+
PIN 2	NC S 2
PIN 3	-
PIN 4	NO S 1
PIN 5	PE
Family construction form	M12
No. of poles	12
Coding	A
Gender	male

black