

## EXACT8, 8XM8, 3 POLE

Conn.M12 12 pole

Art.No.: 8000-88060-0000000

Weight: 0.126 kg

Country of origin: DE

Model designation: MVP8N-GS8D

8-way, 3-pole

M12 (12-pole)




Inline face or side mounting


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

### Link to Product

#### Illustration





Product may differ from Image



#### Header

Material short text MVP8N-GS8D

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/8000-88060-0000000">https://shop.murrelektronik.com/8000-88060-0000000</a>
GTIN	4048879054515
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879054515
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Current operating per contact max.	1,5 A

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	mounted, screwed

**Device protection | Media**

Flame resistance	flame retardant
------------------	-----------------

**Mechanical data | Material data**

Material housing	Plastic
------------------	---------

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	70 °C
----------------------------	-------

Additional condition temperature range	depending on cable quality
--	----------------------------

**Connection type 2**

Family construction form	M12
--------------------------	-----

No. of poles	12
--------------	----

Coding	A
--------	---

Gender	male
--------	------

Color contact carrier	black
-----------------------	-------

PIN 1	24 V DC
-------	---------

PIN 2	0 V
-------	-----

PIN 3	S 1
-------	-----

PIN 4	S 2
-------	-----

PIN 5	S 3
-------	-----

PIN 6	S 4
-------	-----

PIN 7	S 5
-------	-----

PIN 8	S 6
-------	-----

PIN 9	S 7
-------	-----

PIN 10	S 8
--------	-----

PIN 11	S 9
--------	-----

PIN 12	S 10
--------	------

Family construction form	M8
--------------------------	----

No. of poles	3
--------------	---

Coding	A
--------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

PIN 1	+
-------	---

PIN 3	-
-------	---

PIN 4	S
-------	---