

EXACT12, 8XM12, 4 POLE CAP, PLUG. SCREW-TERM.

Art.No.: 8000-88450-0000000

Weight: 0.206 kg

Country of origin: DE

Model designation: MVP12N-FN8V

8-way, 4-pole

Form PNP




Screw plug-in terminals



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration





Product may differ from Image



Header

Material short text MVP12N-FN8V

Commercial data

URL Webshop	https://shop.murrelektronik.com/8000-88450-0000000
GTIN	4048879054164
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879054164
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current max.	8 A

Installation

Connection cross section max.	1,5 mm ²
-------------------------------	---------------------

AWG number max. 16

Installation | Connection

Connection Screw plug-in terminals

Device protection | Electrical

Degree of protection (EN IEC 60529) IP67, IP65

Device protection | Media

Flame resistance flame retardant

Mechanical data | Material data

Material housing Plastic

Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 70 °C

Connection type 2

Family construction form Cap

No. of poles 14

Family construction form M12

No. of poles 4

Coding A

Gender female

Color contact carrier black

PIN 1 +

PIN 2 n.c.

PIN 3 -

PIN 4 NO S 1

PIN 5 PE