

## EXACT12, 8XM12, 5-POLE, BASIC HOUSING, W.O. LED'S

Without homerun-cable

Art.No.: 8000-88502-0000000

Weight: 0.127 Country of origin: DE

Model designation: MVP12N-MK8F-XA

8-way, 5-pole

without LED, up to 125 V AC/DC

Screw plug-in terminals

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


Further cable lengths on request.


## **Link to Product**

## Illustration












stay connected



Product may differ from Image









Header	
Material short text	MVP12N-MK8F-XA
Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-88502-0000000
GTIN	4048879054041
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879054041
Packaging unit	1
Electrical data   Supply	
Operating voltage AC	125 V
Operating voltage DC	125 V
Current operating per contact max.	4 A
Total current max.	8 A
Device protection   Electrical	



Degree of protection (EN IEC 60529)	IP67, IP65
Device protection   Media	
Flame resistance	flame retardant
Mechanical data   Material data	
Material housing	Plastic
Environmental characteristics   Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C