

## Mico Pro electronic circuit protection, 1 channel

IN: 24 V DC OUT: 24 V DC / 4 A CL2

Art.No.: 9000-41011-0400001

Weight: 0.056 kg

Country of origin: CZ

Model designation: Mico Pro fix 1.4 CL2

Mico Pro® fix 1.4

1 channel

Current adjustment 4 A

Build your own Mico Pro® online:


[START](#)

### Link to Product

#### Illustration



Product may differ from Image



#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/9000-41011-0400001">https://shop.murrelektronik.com/9000-41011-0400001</a>
GTIN	4048879772761
Customs tariff number	85363030
ECLASS-6.0	27371802
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-7.1	27371802
ECLASS-8.0	27371802
ECLASS-8.1	27371802
ECLASS-9.0	27371802
ECLASS-9.1	27371802
ECLASS-10.0.1	27371802
ECLASS-10.1	27371802
ECLASS-11.0	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802

ECLASS-13.0	27371802
ECLASS-14.0	27371802
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85363030
EAN	4048879772761
Packaging unit	1

**Electrical data | Supply**

Total current max.	40 A
--------------------	------

**Electrical data | Input**

Input voltage DC min.	9 V
Input voltage DC max.	30 V
Nominal input voltage DC	12 V ... 24 V
Total current bridge set max.	40 A
Control options	via power module
System supply	via power module

**Electrical data | Output**

Number of output channels	1
Triggering current DC full load per channel	3 A
Tolerance trigger current min.	0 %
Tolerance trigger current max.	9 %
Switch-on capacity max.	30 mF

**Installation**

Connection cross-section static min.	0,2 mm <sup>2</sup>
Connection cross section static max.	2,5 mm <sup>2</sup>
Connection cross-section dynamic min.	0,2 mm <sup>2</sup>
Connection cross section dynamic max.	4 mm <sup>2</sup>
AWG number static min.	14
AWG number static max.	24
AWG number dynamic min.	12
AWG number dynamic max.	24

**Installation | Connection**

Connection	Bridge system
------------	---------------

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

**Mechanical data | Mounting data**

Height	130 mm
Width	8 mm
Depth	114 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

**Environmental characteristics | Climatic**

Operating temperature min.	-25 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-40 °C ... 80 °C

**Connection type 6**

Family construction form	Bridging Contact
No. of poles	1
Gender	female

Color contact carrier	black
PIN 1	UB +
Family construction form	Bridging Contact
No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	0 V
Family construction form	Bridging Contact
No. of poles	4
Gender	female
Color contact carrier	black
PIN 1	On
PIN 2	Ctrl
PIN 3	Alarm
PIN 4	0.9
Family construction form	Bridging Contact
No. of poles	4
Gender	male
Color contact carrier	black
PIN 1	On
PIN 2	Ctrl
PIN 3	Alarm
PIN 4	0.9
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	0 V 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 1