

MICO IP67 electronic circuit protection, 4 Channels, 2A

IN: 24 V DC OUT: 24 V DC / 2 A CL2 / Expandable

Art.No.: 9000-41014-0200067

Weight: 0.153

Country of origin: DE

Model designation: Mico67-4.2-CL2

MICO67 4.2 CL2

4 × M12, A-coded NEC CL2, (2 A)



Voltage IN and transmission via M12, L-coded (16 A)

24 V/16 A

24 V/2 A

LED port diagnostic

Limitation of the 4 voltage taps to 2 A (M12, A-coded)

[Link to Product](#)
Illustration


Product may differ from Image


Commercial data

ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
customs tariff number	85363010
GTIN	4048879852272
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67
-------------------------------------	------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	45 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C