

MICO BASIC 4.6 electronic circuit protection, 4 CHANNELS

IN: 24 V DC OUT: 24 V DC / 6 A Art.No.: 9000-41064-0600000

Weight: 0.09

Country of origin: CZ


Model designation: MICO Basic 4.6


MICO BASIC 4.6 4 channels Current adjustment 6 A

Link to Product

Illustration







Product may differ from Image













Header

Material short text MICO Basic 4.6

Commercial data

URL Webshop https://shop.murrelektronik.com/9000-41064-0600000



stay connected

GTIN	4040070222422
	4048879332422
ECLASS-6.0	27371802
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-7.1	27371802
ECLASS-8.0	27371802
ECLASS-8.1	27371802
ECLASS-9.0	27371802
ECLASS-9.1	27371802
ECLASS-10.0.1	27371802
ECLASS-10.1	27371802
ECLASS-11.0	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ECLASS-13.0	27371802
ECLASS-14.0	27371802
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85363010
EAN	4048879332422
Packaging unit	1
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Total current bridge set max.	40 A
ON input voltage control inputs min.	10 V
ON input voltage control inputs max.	30 V
ON pulse length control inputs high min.	20 ms
Electrical data Output	
Switch-on capacity per channel max.	20 mF
Switching current max.	20 mA
Installation	
Connection cross-section inputs max.	16 mm ²
Connection cross-section outputs max.	4 mm ²
Connection cross-section control inputs /	
control outputs max.	2,5 mm ²
Mechanical data Mounting data	
Height	90 mm
Width	36 mm
Depth	80 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Connection type 5	
	Público Ocatest
Family construction form	Bridging Contact

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-19



stay connected

No. of poles	1	
Gender	female	
Color contact carrier	Black	
PIN 1	24 V DC	
Family construction form	Bridging Contact	
No. of poles	1	
Gender	female	
Color contact carrier	Black	
PIN 1	0 V	
Family construction form	terminal	
No. of poles	1	
Gender	female	
Color contact carrier	green	
Connection	Spring clamp terminals FK	
PIN 1	24 V DC	
Family construction form	terminal	
No. of poles	2	
Gender	female	
Color contact carrier	green	
Connection	Spring clamp terminals FK	
PIN 1	On	
PIN 2	14	
Family construction form	terminal	
No. of poles	5	
Gender	female	
Color contact carrier	green	
Connection	Spring clamp terminals FK	
PIN 1	0 V	
PIN 2	Out 1	
PIN 3	Out 2	
PIN 4	Out 3	
PIN 5	Out 4	