

**Emparro IP67 POWER SUPPLY 1-PHASE**

OUT: 24VDC 3,8A - 7/8" 4P NEC - PELV

Art.No.: 9000-11112-1862020  
Weight: 1.22  
Country of origin: CZ  
Model designation: Emparro67 3.8-100-240/24 NEC2 7/8" 4-P


Emparro®67  
INPUT: 90...265 V AC/90...372 V DC  
OUTPUT: 24 V DC (PELV), ±2%  
Current: 3.8 A  
NEC Class 2

**Link to Product**

**Illustration**



Product may differ from Image



**Header**

Material short text                      Emparro67 3.8-100-240/24 NEC2 7/8" 4-P

**Commercial data**

URL Webshop	https://shop.murrelektronik.com/9000-11112-1862020
GTIN	4048879799102
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701

ECLASS-13.0	27040701
ECLASS-14.0	27040701
customs tariff number	85044095
EAN	4048879799102
Packaging unit	1

#### Electrical data

Security level	SELV
----------------	------

#### Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

#### Electrical data | Input

Input voltage AC min.	90 V
Input voltage AC max.	265 V
Input voltage 1 AC	100 V
Input voltage 2 AC	240 V
Input voltage DC min.	90 V
Input voltage DC max.	372 V
Input current at input voltage 1 AC	1.1 A
Input current at input voltage 2 AC	0.5 A
Inrush current max.	89 A @ 230 V
Power factor	230 V AC
Efficiency	91.4 % @ 115 V AC 92.1 % @ 230 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	63 A

#### Electrical data | Output

Output voltage adjustable	no
Output voltage DC	24 V
Output voltage DC min.	23.52 V
Output voltage DC max.	24.48 V
Output current	3.8 A
Mains failure bridging min.	80 ms @ 230 V AC
Spikes (s-s) max.	130 mV
Ripple effective max.	15 mV

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Overload protection output	yes
Short-circuit protection output	yes
Overtemperature protection output	yes

#### Mechanical data | Mounting data

Height	53 mm
Width	111 mm
Depth	141 mm
Suitable for mounting type	6 hole screw mounting

#### Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Derating from	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	4 %
Relative humidity max. (operation)	100 %

#### Conformity

Product standard	IEC 61010-2-201
------------------	-----------------

EMC	EN 55011 B, EN 61000-3-2
-----	--------------------------

Low Voltage Directive	EN 61204-3
-----------------------	------------

**Approvals**

SEMI F47	compliant
----------	-----------

**Connection type 1**

Connection type 1	Output
-------------------	--------

Family construction form	7/8"
--------------------------	------

No. of poles	4
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

PIN 1	24 V DC
-------	---------

PIN 2	24 V DC
-------	---------

PIN 3	0 V PE
-------	--------

PIN 4	0 V PE
-------	--------