

**MICO BASIC 5.2/3.6 ELEC AUX CIRCUIT, 8 CHANNELS**

IN: 24 V DC OUT: 24 V DC / 5x 2 A CL2 &amp; 3x 6 A

Art.No.: 9000-41068-0200600

Weight: 0.16



Country of origin: CZ

Model designation: MICO BASIC 5.2/3.6

MICO BASIC 5.2/3.6

8 channels

Current adjustment 5x 2 A; 3x 6 A

**Link to Product****Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/9000-41068-0200600">https://shop.murrelektronik.com/9000-41068-0200600</a>
GTIN	4048879382373
ECLASS-6.0	27371802
ECLASS-6.1	27371802

ECLASS-7.0	27371802
ECLASS-7.1	27371802
ECLASS-8.0	27371802
ECLASS-8.1	27371802
ECLASS-9.0	27371802
ECLASS-9.1	27371802
ECLASS-10.0.1	27371802
ECLASS-10.1	27371802
ECLASS-11.0	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ECLASS-13.0	27371802
ECLASS-14.0	27371802
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
EAN	4048879382373

**Electrical data | Input**

Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Total current bridge set max.	40 A
ON input voltage control inputs min.	10 V
ON input voltage control inputs max.	30 V
ON pulse length control inputs high min.	20 ms

**Electrical data | Output**

Switch-on capacity per channel max.	20 mF
Switching current max.	20 mA

**Installation**

Connection cross-section inputs max.	16 mm <sup>2</sup>
Connection cross-section outputs max.	4 mm <sup>2</sup>
Connection cross-section control inputs / control outputs max.	2.5 mm <sup>2</sup>

**Mechanical data | Mounting data**

Height	90 mm
Width	70 mm
Depth	80 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

**Environmental characteristics | Climatic**

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C

**Connection type 7**

Family construction form	Bridging Contact
No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	24 V DC
Family construction form	Bridging Contact

No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	0 V
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	0 V
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	On
PIN 2	14
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 1
PIN 2	Out 2
PIN 3	Out 3
PIN 4	Out 4
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 5
PIN 2	Out 6
PIN 3	Out 7
PIN 4	Out 8