

### Mico Pro PS 5-100-240/24

IN: 90 - 265VAC OUT: 24-28V/5ADC / Cover plate included (heavy duty)

Art.No.: 9000-41190-0000105

Weight: 0.440 kg

Country of origin: CZ

Model designation: Mico Pro PS 5-100-240/24

INPUT: 90...265 V AC

OUTPUT: 24...28 V DC

Current: 5 A

Build your own Mico Pro® online:

[START](#)

Mains failure bridging min.


min. 20 ms (115 V AC); min. 65 ms (230 V AC)

### Link to Product

#### Illustration



Product may differ from Image



#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/9000-41190-0000105">https://shop.murrelektronik.com/9000-41190-0000105</a>
GTIN	4048879695664
ECLASS-6.0	27141901
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701

ECLASS-12.0	27040701
ECLASS-13.0	27040701
ECLASS-14.0	27040701
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85044083
EAN	4048879695664
Packaging unit	1

**Electrical data**

Parallel connection	No
Series connection	No

**Electrical data | Supply**

Protective measure	SELV
Power frequency	50 ... 60 Hz

**Electrical data | Input**

Input voltage AC min.	90 V
Input voltage AC max.	265 V
Nominal input voltage AC	115 V ... 230 V
Nominal current AC	1.1 A @ 115 V, 2.3 A @ 230 V
Inrush current max.	30 A
Power factor	115 V AC @ 230 V AC
Efficiency	89.4 % @ 115 V AC 90.8 % @ 230 V AC
Characteristic back-up fuse	Inertia
Fuse protection primary side internal	3,15 A
ON input voltage control inputs min.	9 V
ON input voltage control inputs max.	30 V
CTRL signal	ON/OFF
CTRL input voltage control inputs high min.	9 V
CTRL input voltage control inputs high max.	30 V
ON pulse length control inputs high min.	120 ms

**Electrical data | Output**

Output voltage adjustable	Yes
Output voltage DC	24 V
Output voltage DC min.	24 V
Output voltage DC max.	28 V
Output current	5 A
Spikes (s-s) max.	230 mV
Ripple effective max.	15 mV
Switching voltage AC max.	30 V
Switching voltage DC max.	30 V

**Installation | Connection**

Connection	Push-In spring clamp terminals
------------	--------------------------------

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20
Overload protection output	Yes
Short-circuit protection output	Yes
Overtemperature protection output	Yes

**Mechanical data | Mounting data**

Height	130 mm
--------	--------

Width	54 mm
Depth	114 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

**Environmental characteristics | Electromagnetic compatibility**

Interference emission	IEC 61000-3-2
-----------------------	---------------

**Environmental characteristics | Climatic**

Operating temperature min.	-25 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-40 °C ... 85 °C
Relative humidity (operation)	5 % ... 95 %
Additional condition relative humidity	no condensation

**Conformity**

Product standard	EN IEC 61010-2-201, EN 61204-3
------------------	--------------------------------