

**MODL. VARIO 4-way fixed housing type B**

nickel plated aluminum

Art.No.: M1850-040601

Weight: 0.091

Country of origin: DE

Model designation: EIS-Flansch body socket 4-fach

Stationary housing (round)

4-way

Aluminum

Screw locking

Good chemical and oil resistance (oil resistance does not apply to use with PVC cable)

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
customs tariff number	85389099
GTIN	4048879572965
GTIN	4048879572965
Packaging unit	1
Packaging unit	1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

**Mechanical data**

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-11

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Operating pressure min.	-0,8 bar
-------------------------	----------

Operating pressure max.	16 bar
-------------------------	--------

**Mechanical data | Material data**

Material housing	Aluminum die casting
------------------	----------------------

Coating housing	powder-coated
-----------------	---------------

**Mechanical data | Mounting data**

Mounting method	screw fixing
-----------------	--------------

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	120 °C
----------------------------	--------