

MICO electronic circuit protection, 4 CHANNELS

IN: 24 V DC OUT: 24 V DC / 2x 1-2-3-4 A & 2x 4-6-8-10 A

Art.No.: 9000-41034-0101000

Weight: 0.158 Country of origin: CZ

Model designation: MICO 4.4.10 ACTUATOR - SENSOR

MICO 4.4.10 ACTUATOR-SENSOR


4 channels


Current adjustment 2x 1 A, 2 A, 3 A, 4 A; 2x 4 A, 6 A, 8 A, 10 A

Link to Product

Illustration







Product may differ from Image











Header

Material short text

MICO 4.4.10 ACTUATOR - SENSOR

Commercial data

URL Webshop

https://shop.murrelektronik.com/9000-41034-0101000



stay connected

GTIN	4048879294515
ECLASS-6.0	27371802
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-7.1	27371802
ECLASS-8.0	27371802
ECLASS-8.1	27371802
ECLASS-9.0	27371802
ECLASS-9.1	27371802
ECLASS-10.0.1	27371802
ECLASS-10.1	27371802
ECLASS-11.0	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ECLASS-13.0	27371802
ECLASS-14.0	27371802
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85363010
EAN	4048879294515
Packaging unit	1
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Total current bridge set max.	40 A
ON input voltage control inputs min.	10 V
ON input voltage control inputs max.	30 V
ON pulse length control inputs high min.	20 ms
Electrical data Output	
Switch-on capacity per channel max.	20 mF
Switching voltage AC max.	30 V
Switching voltage DC max.	30 V
Switching current max.	100 mA
Installation	
Connection cross-section inputs max.	16 mm ²
Connection cross-section outputs max.	4 mm ²
Connection cross-section control inputs / control outputs max.	2,5 mm ²
Mechanical data Mounting data	
Height	90 mm
Width	70 mm
Depth	80 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Ambient temperature (storage, transport)	-40 °C
Connection type 11	



stay connected

Eamily construction form	
Family construction form	Bridging Contact
No. of poles	1
Gender	Female
Color contact carrier	black
PIN 1	24 V DC
Family construction form	Bridging Contact
No. of poles	1
Gender	Female
Color contact carrier	black
PIN 1	0 V
Family construction form	Bridging Contact
No. of poles	2
Gender	Female
Color contact carrier	black
PIN 1	On
PIN 2	13
Family construction form	Bridging Contact
No. of poles	2
Gender	Female
Color contact carrier	black
PIN 1	On
PIN 2	14
Family construction form	terminal
No. of poles	1
Gender	Female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC
Family construction form	terminal
No. of poles	1
Gender	Female
Color contact carrier	green
Connection PIN 1	Spring clamp terminals FK 0 V
Family construction form	terminal
No. of poles	2
Gender	Female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 1
PIN 2	Out 1
Family construction form	terminal
No. of poles	2
Gender	Female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 2
PIN 2	Out 2
Family construction form	terminal
No. of poles	2
Gender	Female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 3



PIN 2	Out 3
Family construction form	terminal
No. of poles	2
Gender	Female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 4
PIN 2	Out 4
Family construction form	terminal
No. of poles	4
Gender	Female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	On
PIN 2	On
PIN 3	13
PIN 4	14